



Leitfähige Scharnierdeckelbehälter mit leitfähiger Steckschaumeinlage von 6 mm.

Conductive hinged lid boxes with conductive foam insert of 6 mm.

| Innenabmessungen<br><i>internal dimensions</i> | Tiefe Unterteil<br><i>bottom height</i> | Bestellnr.<br><i>order-no.</i> |
|--|---|--------------------------------|
| 36 x 36 x 11 mm                                | 6 mm                                    | <b>C-199 2223</b>              |
| 74 x 51 x 21 mm                                | 14 mm                                   | <b>C-186 203</b>               |
| 80 x 54 x 17 mm                                | 12 mm                                   | <b>C-186 074</b>               |
| 90 x 64 x 19 mm                                | 13 mm                                   | <b>C-199 2231</b>              |
| 108 x 83 x 13 mm                               | 10 mm                                   | <b>C-186 228</b>               |
| 180 x 103 x 30 mm                              | 28 mm                                   | <b>C-186 258</b>               |
| 228 x 125 x 20 mm                              | 10 mm                                   | <b>C-186 256</b>               |
| 228 x 125 x 30 mm                              | 20 mm                                   | <b>C-186 257</b>               |
| 253 x 152 x 38 mm                              | 38 mm                                   | <b>C-199 2237</b>              |

|  | Behälter<br>box                      | Steckschaum<br>foam                |
|--|--------------------------------------|------------------------------------|
| Material<br>material                       | Polypropylen<br><i>polypropylene</i> | Polyurethan<br><i>polyurethane</i> |
| Widerstand<br>resistance                   | ca. $10^4 \Omega$                    | ca. $10^3 - 10^4 \Omega$           |
| Farbe<br>color                             | schwarz / black                      |                                    |
| Raumgewicht<br>density                     | 40 kg / m <sup>3</sup>               |                                    |
| Stauchhärte<br>Compression load deflection | 50 kPa (40%)                         |                                    |