


Sonderformen

DIN 582

Ringmuttern



weitere Produktinformationen → TI-148

* Abmessung nicht genormt,

Maße der nächst größeren Abmessung

Maße	M 6*	M 8	M 10	M 12	M 14*	M 16	M 18*	M 20	M 22*
d ₁	17	20	25	30	35	35	40	40	45
d ₂	28	36	45	54	63	63	72	72	81
d ₃	16	20	25	30	35	35	40	40	45
m	8,5	8,5	10	11	13	13	16	16	18
h	31	36	45	53	62	62	71	71	80,5
k	6	8	10	12	14	14	16	16	18

Maße	M 24	M 27*	M 30	M 33*	M 36	M 42	M 48	M 56	
d ₁	50	50	65	65	75	85	100	110	
d ₂	90	90	108	108	126	144	166	184	
d ₃	50	50	60	60	70	80	90	100	
m	20	20	25	25	30	35	40	45	
h	90	90	109	109	128	147	168	187	
k	20	20	24	24	28	32	38	42	