

- Up to 96% efficiency – No heat-sink required
- Pin compatible with LMxx linear regulators
- SIP-package fits existing TO-220 footprint
- Built in filter capacitors
- Operation temp. range  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$
- Short circuit protection
- Wide input operating range
- Excellent line / load regulation
- Low standby current
- 3-year product warranty



The TSR 1 series step-down switching regulators are drop-in replacement for inefficient 78xx linear regulators. A high efficiency up to 96% allows full load operation up to  $+60^{\circ}\text{C}$  ambient temperature without the need of any heat-sink or forced cooling. The TSR 1 switching regulators provide other significant features over linear regulators, i.e. better output accuracy ( $\pm 2\%$ ), lower standby current of 2 mA and no requirement of external capacitors. The high efficiency and low standby power consumption makes these regulators an ideal solution for many battery powered applications.

### Models

| Order Code  | Output Current max. | Input Voltage Range        | Output Voltage nom. | Efficiency typ.    |
|-------------|---------------------|----------------------------|---------------------|--------------------|
| TSR 1-2412  | 1'000 mA            | 4.6 - 36 VDC (9 VDC nom.)  | 1.2 VDC             | 74 % (at Vin min.) |
| TSR 1-2415  |                     |                            | 1.5 VDC             | 78 % (at Vin min.) |
| TSR 1-2418  |                     |                            | 1.8 VDC             | 82 % (at Vin min.) |
| TSR 1-2425  |                     |                            | 2.5 VDC             | 87 % (at Vin min.) |
| TSR 1-2433  |                     |                            | 3.3 VDC             | 91 % (at Vin min.) |
| TSR 1-2450  |                     | 6.5 - 36 VDC (12 VDC nom.) | 5 VDC               | 94 % (at Vin min.) |
| TSR 1-2465  |                     | 9 - 36 VDC (12 VDC nom.)   | 6.5 VDC             | 93 % (at Vin min.) |
| TSR 1-2490  |                     | 12 - 36 VDC (24 VDC nom.)  | 9 VDC               | 95 % (at Vin min.) |
| TSR 1-24120 |                     | 15 - 36 VDC (24 VDC nom.)  | 12 VDC              | 95 % (at Vin min.) |
| TSR 1-24150 |                     | 18 - 36 VDC (24 VDC nom.)  | 15 VDC              | 96 % (at Vin min.) |

Note - For input voltage higher than 32 VDC an external input capacitor (22  $\mu\text{F}$ ) is required.

### Input Specifications

|                          |                |  |
|--------------------------|----------------|--|
| Input Current            | - At no load   | 9 Vin models: <b>1 mA typ.</b><br>12 Vin models: <b>1 mA typ.</b><br>24 Vin models: <b>1 mA typ.</b>   |
|                          | - At full load | 9 Vin models: <b>1'000 mA max.</b><br>12 Vin models: <b>1'000 mA max.</b><br>24 Vin models: <b>1'000 mA max.</b><br>(at Vin min.)  |
| Reflected Ripple Current |                | <b>150 mAp-p typ.</b>  |
| Recommended Input Fuse   | - 9 Vin input  | 1.2 Vout models: <b>630 mA</b> (slow blow)<br>1.5 Vout models: <b>800 mA</b> (slow blow)<br>1.8 Vout models: <b>800 mA</b> (slow blow)<br>2.5 Vout models: <b>1'250 mA</b> (slow blow)<br>3.3 Vout models: <b>1'250 mA</b> (slow blow) |
|                          | - 12 Vin input | 5 Vout models: <b>1'600 mA</b> (slow blow)   |
|                          | - 24 Vin input | 6.5 Vout models: <b>1'250 mA</b> (slow blow)<br>9 Vout models: <b>1'250 mA</b> (slow blow)<br>12 Vout models: <b>1'600 mA</b> (slow blow)<br>15 Vout models: <b>1'600 mA</b> (slow blow)   |
|                          |                | (The need of an external fuse has to be assessed in the final application.)  |
| Input Filter             |                | <b>Internal Capacitor</b>  |

### Output Specifications

|  |                                 |  |
|--|---------------------------------|--|
| Voltage Set Accuracy                   |                                 | <b>±2% max.</b>  |
| Regulation                             | - Input Variation (Vmin - Vmax) | <b>0.2% max.</b>   |
|  | - Load Variation (10 - 100%)    | <b>0.6% max.</b> (1.2 & 1.5 Vout models)   |
|  |                                 | <b>0.4% max.</b> (other models)  |
| Ripple and Noise<br>(20 MHz Bandwidth) |                                 | 9 Vin models: <b>50 mVp-p typ.</b><br>12 Vin models: <b>50 mVp-p typ.</b><br>24 Vin models: <b>75 mVp-p typ.</b> |
| Capacitive Load                        |                                 | <b>470 µF max.</b>   |
| Minimum Load                           |                                 | <b>Not required</b>  |
| Temperature Coefficient                |                                 | <b>±0.015 %/K max.</b>   |
| Start-up Overshoot Voltage             |                                 | <b>1% max.</b>   |
| Short Circuit Protection               |                                 | <b>Continuous, Automatic recovery</b>  |
| Output Current Limitation              |                                 | <b>250% typ. of Iout max.</b>  |
| Transient Response                     | - Peak Variation                | <b>150 mV typ. / 200 mV max.</b> (50% Load Step)   |
|  | - Response Time                 | <b>250 µs typ. / 350 µs max.</b> (50% Load Step)   |

### EMC Specifications

|               |                           |  |
|---------------|---------------------------|--|
| EMI Emissions | - Conducted Emissions     | <b>EN 55032 class A</b> (with external filter)   |
|               | - Radiated Emissions      | <b>EN 55032 class A</b> (with external filter)   |
|               | External filter proposal: | <a href="http://www.tracopower.com/overview/tsr1">www.tracopower.com/overview/tsr1</a> |

### General Specifications

|                       |                         |  |
|-----------------------|-------------------------|--|
| Relative Humidity     |                         | <b>95% max.</b> (non condensing)   |
| Temperature Ranges    | - Operating Temperature | <b>-40°C to +85°C</b>  |
|                       | - Storage Temperature   | <b>-55°C to +125°C</b>   |
| Power Derating        | - High Temperature      | <b>2.4 %/K above 60°C</b>  |
|                       |                         | See application note: <a href="http://www.tracopower.com/overview/tsr1">www.tracopower.com/overview/tsr1</a> |
| Over Temperature      | - Protection Mode       | <b>150°C typ.</b> (Automatic recovery)   |
| Protection Switch Off | - Measurement Point     | <b>Internal IC temperature</b>   |
| Cooling System        |                         | <b>Natural convection</b> (20 LFM)   |

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

|                          |  |  |
|--------------------------|--|--|
| Switching Frequency      |  | 400 - 600 kHz (PWM)<br>500 kHz typ. (PWM)  |
| Insulation System        |  | Non-isolated   |
| Reliability              | - Calculated MTBF  | 25'710'000 h (MIL-HDBK-217F, ground benign)  |
| Washing Process          |  | According to Cleaning Guideline<br><a href="http://www.tracopower.com/info/cleaning.pdf">www.tracopower.com/info/cleaning.pdf</a>  |
| Environment              | - Vibration<br>- Thermal Shock   | MIL-STD-810F<br>MIL-STD-810F   |
| Housing Material         |  | Non-conductive Plastic (UL 94 V-0 rated)   |
| Potting Material         |  | Silicone (UL 94 V-0 rated)   |
| Pin Material             |  | Copper   |
| Pin Foundation Plating   |  | Nickel (2 - 3 µm)  |
| Pin Surface Plating      |  | Tin (3 - 5 µm), matte  |
| Housing Type             |  | Plastic Case   |
| Mounting Type            |  | PCB Mount  |
| Connection Type          |  | THD (Through-Hole Device)  |
| Footprint Type           |  | SIP3   |
| Soldering Profile        |  | Lead-Free Wave Soldering<br>265°C / 10 s max.  |
| Weight                   |  | 1.9 g  |
| Environmental Compliance | - REACH Declaration<br><br>- RoHS Declaration<br><br>- SCIP Reference Number | <a href="http://www.tracopower.com/info/reach-declaration.pdf">www.tracopower.com/info/reach-declaration.pdf</a><br>REACH SVHC list compliant<br>REACH Annex XVII compliant<br><a href="http://www.tracopower.com/info/rohs-declaration.pdf">www.tracopower.com/info/rohs-declaration.pdf</a><br>Exemptions: 7a, 7c-I<br>(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule))<br>9d15ed19-93d9-4ef5-b2ab-a4e3f77f58e2 |


## Supporting Documents

Overview Link (for additional Documents)

[www.tracopower.com/overview/tsr1](http://www.tracopower.com/overview/tsr1)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

**Outline Dimensions**



| Pinout |          |
|--------|----------|
| Pin    | Function |
| 1      | +Vin     |
| 2      | GND      |
| 3      | +Vout    |

Dimensions in mm (inch)  
 Tolerances: ±0.5 (±0.02)  
 Pin pitch tolerances: ±0.25 (±0.01)  
 Pins: ±0.05 (±0.002)