



Vogt Verbindungstechnik

Steckungen für gedruckte Schaltungen

Masse im Steckbereich
 DIN 46342 Teil 1


Languettes plates pour circuits imprimés

Dimensions zone d'emboîtement selon
 DIN 46342 partie 1


Mounting tabs for printed circuitry

Dimensions in the tab sector
 DIN 46342 part 1


2,8 mm




Artikel-Nr. Numéro d'article Part-No.	3773B08.6() MS	03773B08.6() MS	3775B05.6() MS	03775B05.6() MS	3775B08.6() MS	03775B08.6() MS	377108.6() MS
Print Bohrung Trou Hole	Ø 1.3 T 7.0 L 7.0 L1 16.1 B1 3.8 B2 2.8 D 1.2x3.0 B 1.4 S 0.8	Ø 1.3 T 7.0 L 7.0 L1 16.1 B1 3.8 B2 2.8 D 1.2x3.0 B 1.4 S 0.8	Ø 1.3 T 7.0 L 7.0 L1 16.1 B1 3.8 B2 2.8 D 1.3 B 1.4 S 0.5	Ø 1.3 T 7.0 L 7.0 L1 16.1 B1 3.8 B2 2.8 D 1.3 B 1.4 S 0.5	Ø 1.3/1.4 T 7.0 L 7.0 L1 16.1 B1 3.8 B2 2.8 D 1.3 B 1.4 S 0.8	Ø 1.3 T 7.0 L 7.0 L1 16.1 B1 3.8 B2 2.8 D 1.3 B 1.4 S 0.8	Ø 1.3 T 7.5 L 10.0 L1 17.5 B1 2.8 B2 2.8 D 1.2 B 1.3 S 0.8
Stand.-Packg.	2000	5000	2000	4800	2000	5000	2000
Werkzeuge Outils / Tools	1035/18	104808	1035/17	104805	1035/18	104808	1035/16



Artikel-Nr. Numéro d'article Part-No.	0377108.6() MS	3779L.6() MS	3773C05.2() BZ 3773C05.6() MS	03773C05.2() BZ 03773C05.6() MS	3773E05.2() BZ	3779.6() MS	03779.6() MS
Print Bohrung Trou Hole	Ø 1.3 T 7.5 L 10.0 L1 17.5 B1 2.8 B2 2.8 D 1.2 B 1.3 S 0.8	Ø 1.4 siehe Seite 115 voir page 115 see page 115	Ø 1.4 T 3.2 L 7.0 L1 12.3 B1 3.8 B2 2.8 D 1.3x3.1 B 1.5 S 0.5	Ø 1.4 T 3.2 L 7.0 L1 12.3 B1 3.8 B2 2.8 D 1.3x3.1 B 1.5 S 0.5	Ø 1.4 T 3.2 L 7.0 L1 12.3 B1 3.8 B2 2.8 D - B 1.5 S 0.5	Ø 1.4 T 4.0 L 7.0 L1 12.5 B1 5.0 B2 2.8 D 1.3x2.4 B 1.4 S 0.5	Ø 1.3/1.4 T 4.0 L 7.0 L1 12.5 B1 5.0 B2 2.8 D 1.3x2.4 B 1.4 S 0.5
Stand.-Packg.	5000		2000	4800	2000	2000	4800
Werkzeuge Outils / Tools	104708		1035/17	104805	1035/17	1035/17	1043B



Flachsteckhülsen Clips femelles Receptacles



für Steckungen
 pour languettes plates
 for mounting tabs

Artikel-Nr. Numéro d'article Part-No.	3779WR.2() BZ	1019E.6() MS	1019F.2() BZ	3785F04.6() MS	3785F05.2() BZ 3785F05.6() MS	3785F08.6() MS
Print Bohrung Trou Hole	Ø 1.5/1.6 T 4.3 L 6.8 L1 12.5 B1 5.0 B2 2.8 D 1.2 B ø1.5 S 0.5	Ø 1.6 siehe Seite 130 voir page 130 see page 130	Ø 1.6 siehe Seite 130 voir page 130 see page 130	Ø 1.3 B2 2.8x0.4 T 4.0 L 8.0 L2 6.0 B1 1.8 A 2.5 B 1.3 S 0.25	Ø 1.3 B2 2.8x0.5 T 4.0 L 8.0 L2 6.0 B1 1.9 A 2.5 B 1.3 S 0.25	Ø 1.3 B2 2.8x0.8 T 4.0 L 8.0 L2 6.0 B1 2.0 A 2.5 B 1.3 S 0.25
Stand.-Packg.	2000			2000	2000	2000
Werkzeuge Outils / Tools	1035/13			1037/35	1037/35	1037/35