



# Vogt Verbindungstechnik

## Steckungen für gedruckte Schaltungen

Masse im Steckbereich  
 DIN 46342 Teil 1


## Languettes plates pour circuits imprimés

Dimensions zone d'emboîtement selon  
 DIN 46342 partie 1




## Mounting tabs for printed circuitry

Dimensions in the tab sector  
 DIN 46342 part 1

**4,8 mm**




Artikel-Nr. Numéro d'article → Part-No.	<b>3825C08.2( ) BZ</b> <b>3825C08.6( ) MS</b>	<b>03825C08.2( ) BZ</b> <b>03825C08.6( ) MS</b>
Print Bohrung → Trou Hole	∅ 1.4 T 2.6 L 6.4 L1 11.2 B1 6.4 A 5.0 D 1.5 B 1.35 S 0.8	∅ 1.4 T 2.6 L 6.4 L1 11.2 B1 6.4 A 5.0 D 1.5 B 1.35 S 0.8
Stand.-Packg.	2000	2000
Werkzeuge Outils / Tools	<b>1037/22</b>	<b>1045C</b>



Artikel-Nr. Numéro d'article → Part-No.	<b>3827H.2( ) BZ</b>	<b>03827H.2( ) BZ</b>	<b>3827R05.6( ) MS</b>
Print Bohrung → Trou Hole	∅ 1.4 T 4.0 L 7.0 L1 13.0 B1 13.0 A 5.0 D 1.4 B 1.3 S 0.8	∅ 1.4 T 4.0 L 7.0 L1 13.0 B1 13.0 A 5.0 D 1.4 B 1.3 S 0.8	∅ 1.3 T 4.0 L 7.0 L1 13.0 B1 25.7 A 5.0/7.62 D 1.4 B 1.25 S 0.5
Stand.-Packg.	1000	2000	1000
Werkzeuge Outils / Tools	-	<b>1045H</b>	-

### Flachsteckhülsen Clips femelles Receptacles



für Steckungen  
 pour languettes plates  
 for mounting tabs

Artikel-Nr. Numéro d'article Part-No.	<b>3826F05.6( ) MS</b>	<b>3826F08.6( ) MS</b>
Print Bohrung → Trou Hole	∅ 1.3 B2 <b>4.8x0.5</b> T 4.0 L 8.0 L2 7.5 B1 2.6 A 5.0 B 1.3 S 0.35	∅ 1.3 B2 <b>4.8x0.8</b> T 4.0 L 8.0 L2 7.5 B1 2.7 A 5.0 B 1.3 S 0.35
Stand.-Packg.	1000	1000
Werkzeuge Outils / Tools	<b>1037/36</b>	<b>1037/36</b>