



<b>ITEM-NO. (ITEM-NO.)</b>	2091-1423
<b>Measured voltage (Measured voltage / V)</b>	160
<b>Measured shock voltage (Measured shock voltage / kV)</b>	2.5
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	10
<b>RM (PIN SPACING / mm)</b>	3.5
<b>P (NO. OF POLES)</b>	3
<b>Height (Height / mm)</b>	12.4
<b>Width (Width / mm)</b>	12.5
<b>Depth (Depth / mm)</b>	17.5
<b>COLOR (COLOR)</b>	lichtgrau
<b>Comment (Comment)</b>	$L = (\text{No. of poles} - 1) \times \text{Pin Spacing} + 5.5 \text{ mm}$
<b>Dimensions (Dimensions)</b>	1.2 +0.1 mm