

Kupfer-Aderendhülsen ohne Isolation

DIN 46228, Teil 1, ausgenommen*

Embouts de fil en cuivre sans isolation

DIN 46228, partie 1, excepté*

Uninsulated copper ferrules

DIN 46228, part 1, except*

Werkstoff:

E-CU = Elektrolytkupfer

Oberflächenbehandlung: Code
 bl = blank (0)
 ag = versilbert (1)
 sn = verzinkt (7)

Matière:

E-CU = cuivre électrolytique

Traitements de surface: Code
 bl = brut (0)
 ag = argenté (1)
 sn = étamé (7)

Material:

E-CU = electrolytic copper

Surface-plating: Code
 bl = clean (0)
 ag = silver-plated (1)
 sn = tin-plated (7)

Bestellbeispiel:
 Exemple de commande:
 Example of order:

440005.47
 (4400/05 CU sn)



mm ² (AWG)	Artikel-Nr. Numéro d'article Part-No.	DIN 46 228/1	øD1 mm	øD2 mm	L1 mm	S mm	Stand- Packg.	Werkzeuge Outils Tools	mm ² (AWG)	Artikel-Nr. Numéro d'article Part-No.	DIN 46 228/1	øD1 mm	øD2 mm	L1 mm	S mm	Stand- Packg.	Werkzeuge Outils Tools										
0.1-0.3 (26-24)	440005.4()	*	0.8	1.7	5	0.15	5000	3984H 4517 4536 4542	6 (10)	440710.4()	6-10	3.5	4.7	10	0.2	1000	3984J 4521 4523N 4526N 4531 4536 4542										
	440007.4()	*	0.8	1.7	7	0.15	5000			440712.4()	6-12	3.5	4.7	12	0.2	1000		440715.4()	6-15	3.5	4.7	15	0.2	1000	440718.4()	6-18	3.5
0.5 (22)	440106.4()	0.5-6	1	2.1	6	0.15	5000	3984H 4518N 4523N 4527 4531 4536 4542	10 (8)	440812.4()	10-12	4.5	5.8	12	0.2	1000	3984J 4521 4522 4526N										
	440108.4()	*	1	2.1	8	0.15	5000			440815.4()	10-15	4.5	5.8	15	0.2	1000		440818.4()	10-18	4.5	5.8	18	0.2	1000			
	440110.4()	0.5-10	1	2.1	10	0.15	5000			440820.4()	*	4.5	5.8	20	0.2	1000		440825.4()	*	4.5	5.8	25	0.2	1000			
	440112.4()	*	1	2.1	12	0.15	5000																				
0.75 (20)	440206.4()	0.75-6	1.2	2.3	6	0.15	5000	3984H 4518N 4521 4523N 4527 4531 4536 4542	16 (6)	440912.4()	16-12	5.8	7.5	12	0.2	1000	3984J 4522 4526N										
	440208.4()	*	1.2	2.3	8	0.15	5000			440915.4()	16-15	5.8	7.5	15	0.2	1000		440918.4()	16-18	5.8	7.5	18	0.2	1000			
	440210.4()	0.75-10	1.2	2.3	10	0.15	5000			440920.4()	*	5.8	7.5	20	0.2	1000		440925.4()	16-25	5.8	7.5	25	0.2	1000			
	440212.4()	*	1.2	2.3	12	0.15	5000			440930.4()	*	5.8	7.5	30	0.2	1000		440932.4()	16-32	5.8	7.5	32	0.2	1000			
440220.4()	*	1.2	2.3	20	0.15	2000																					
1 (18)	440306.4()	1-6	1.4	2.5	6	0.15	5000	3984H 4518N 4521 4523N 4527 4531 4536 4542	25 (4)	441012.4()	*	7.3	9.5	12	0.2	1000	4522 4538N 4539N										
	440308.4()	*	1.4	2.5	8	0.15	5000			441015.4()	25-15	7.3	9.5	15	0.2	1000		441018.4()	25-18	7.3	9.5	18	0.2	1000			
	440310.4()	1-10	1.4	2.5	10	0.15	5000			441020.4()	*	7.3	9.5	20	0.2	1000		441025.4()	25-25	7.3	9.5	25	0.2	1000			
	440312.4()	*	1.4	2.5	12	0.15	5000			441028.4()	*	7.3	9.5	28	0.2	1000		441032.4()	25-32	7.3	9.5	32	0.2	1000			
440320.4()	*	1.4	2.5	20	0.15	2000																					
1.5 (16)	440406.4()	*	1.7	2.8	6	0.15	5000	3984H 4518N 4521 4523N 4527 4531 4536 4542	35 (2)	441112.4()	*	8.3	11	12	0.2	500	4522 4538N										
	440407.4()	1.5-7	1.7	2.8	7	0.15	5000			441115.4()	*	8.3	11	15	0.2	500		441118.4()	35-18	8.3	11	18	0.2	500			
	440408.4()	*	1.7	2.8	8	0.15	5000			441120.4()	*	8.3	11	20	0.2	500		441125.4()	35-25	8.3	11	25	0.2	500			
	440410.4()	1.5-10	1.7	2.8	10	0.15	5000			441130.4()	*	8.3	11	30	0.2	500		441132.4()	35-32	8.3	11	32	0.2	500			
	440412.4()	1.5-12	1.7	2.8	12	0.15	5000																				
	440415.4()	*	1.7	2.8	15	0.15	5000																				
	440418.4()	1.5-18	1.7	2.8	18	0.15	5000																				
	440420.4()	*	1.7	2.8	20	0.15	2000																				
2.5 (14)	440506.4()	*	2.2	3.4	6	0.15	5000	3984H 4521 4523N 4531 4536 4542	50 (1/0)	441218.4()	50-18	10.3	13	18	0.3	500	4537 4539N										
	440507.4()	2.5-7	2.2	3.4	7	0.15	5000			441220.4()	*	10.3	13	20	0.3	500		441222.4()	*	10.3	13	22	0.3	500			
	440508.4()	*	2.2	3.4	8	0.15	5000			441225.4()	50-25	10.3	13	25	0.3	500		441230.4()	*	10.3	13	30	0.3	500			
	440510.4()	2.5-10	2.2	3.4	10	0.15	2000			441232.4()	50-32	10.3	13	32	0.3	500											
	440512.4()	2.5-12	2.2	3.4	12	0.15	2000																				
	440515.4()	*	2.2	3.4	15	0.15	2000																				
	440518.4()	2.5-18	2.2	3.4	18	0.15	2000																				
	440520.4()	*	2.2	3.4	20	0.15	2000																				
440530.4()	*	2.2	3.4	30	0.15	2000																					
4 (12)	440608.4()	*	2.8	4	8	0.2	2000	3984H 4521 4523N 4531 4536 4542	70 (2/0)	441322.4()	*	12.5	15	22	0.4	100	4537										
	440609.4()	4-9	2.8	4	9	0.2	2000			441325.4()	*	12.5	15	25	0.4	100		441332.4()	*	12.5	15	32	0.4	100			
	440610.4()	*	2.8	4	10	0.2	2000																				
	440612.4()	4-12	2.8	4	12	0.2	2000																				
	440615.4()	4-15	2.8	4	15	0.2	2000																				
	440618.4()	4-18	2.8	4	18	0.2	2000																				
	440620.4()	*	2.8	4	20	0.2	1000																				
	440630.4()	*	2.8	4	30	0.2	1000																				
95 (3/0)	441425.4()	*	14.5	17	25	0.4	100	3984H 4521 4523N 4531 4536 4542	95 (3/0)	441432.4()	*	14.5	17	32	0.4	100											
	441432.4()	*	14.5	17	32	0.4	100																				