

Flachsteckhülsen

DIN 46247, Teil 3
DIN 46340, Teil 3 zum Einrasten in Tüllen

Clips femelles plats

DIN 46247, partie 3
DIN 46340, partie 3 pour encliqueter dans des boîtiers

Flat receptacles

DIN 46247, part 3
DIN 46340, part 3 to engage in housings

6,3 mm

Werkstoff:
BZ = Bronze
MS = Messing
ST = Stahl

Matière:
BZ = bronze
MS = laiton
ST = acier

Material:
BZ = bronze
MS = brass
ST = steel

Strombelastbarkeit:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.
4.0 - 6.0 mm² / 25 A max.

Intensité admissible:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.
4.0 - 6.0 mm² / 25 A max.

Current carrying capacity:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.
4.0 - 6.0 mm² / 25 A max.





Oberflächenbehandlung: Code
bl = blank (0)
ag = versilbert (1)
au = vergoldet (2)
ni = vernickelt (5)
sn = reinverzinkt (7)

Traitements de surface: Code
bl = brut (0)
ag = argenté (1)
au = doré (2)
ni = nickelé (5)
sn = étamage pur (7)

Surface-plating: Code
bl = clean (0)
ag = silver-plated (1)
au = gold-plated (2)
ni = nickel plated (5)
sn = pure tin-plated (7)

Bestellbeispiel:
Exemple de commande:
Example of order:

3831.67
(3831 MS sn)



mm ² (AWG)	für Steckungen pour languettes for tabs	Artikel-Nr. Numéro d'article Part-No.	DIN	L1 mm	L2 mm	L3 mm	A1 mm	A2 mm	S mm	Stand- Packg	Werkzeuge Outils Tools
0.5-1 (22-18)	6.3 x 0.8	3831.6() MS	46247/T3	19	7.5	4	9	4.5	0.45	1000	3988N 3984A
	6.3 x 0.8	3831.95 ST ni	46247/T3	19	7.5	4	9	4.5	0.45	1000	
0.5-1.5 (22-16)	6.3 x 0.8	3832.6() MS	46247/T3	19	7.5	4	9	4.5	0.45	1000	3988N 3984A
	6.3 x 0.8	3832.95 ST ni	46247/T3	19	7.5	4	9	4.5	0.45	1000	
1-2.5 (18-14)	6.3 x 0.8	3833.27 BZ sn	46247/T3	19	7.5	4	8.5	4	0.4	1000	3975C
	6.3 x 0.8	3833.6() MS	46247/T3	19	7.5	4	8.5	4	0.4	1000	3988N
	6.3 x 0.8	3833.95 ST ni	46247/T3	19	7.5	4	8.5	4	0.4	1000	3984A
4-6 (12-10)	6.3 x 0.8	3835A.67 MS sn	46247/T3	19	7.5	4	9	4.5	0.45	500	3975C
	6.3 x 0.8	3835.95 St ni	46247/T3	19	7.5	4	9	4.5	0.45	500	3988N 3984B
1.5-2.5 (16-14)	6.3 x 0.8	3832D.6() MS	46340/T3	19	7.5	7.3	8.5	4	0.4	1000	3975C 3988N 3984A
4-6 (12-10)	6.3 x 0.8	3835.6() MS	46247/T3	19	7.5	4	9	4.5	0.45	500	3975C 3988N 3984A
0.5-1 (22-18)	6.3 x 0.8	3832W.6() MS		15.2	7.5	4	9	4.5	0.45	1000	3988N 3984A
1.5-2.5 (16-14)	6.3 x 0.8	3833W.6() MS		15.2	7.5	4	9	4.5	0.45	1000	3975C 3988N 3984A