

MATERIAL SAFETY DATA SHEET

Document Number: LSCM2016-15

Issued and Revised Date: 2016 Dec.19

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

PRODUCT IDENTIFICATION

BL-5C (1020mAh) Prismatic Rechargeable Lithium-Ion Battery

MANUFACTURER

Tianjin Lishen Battery Co. Ltd

ADDRESS

6 Lanyuan Road, Huayuan Hi-Tech Industry Park, TianJin, China.

DATE :

2016-12-19

TELEPHONE:

86-022-83710366

FAX:

86-022-83710375

2. COMPOSITION INFORMATION

INGREDIENTS	%	CAS NUMBER
Aluminum Foil	2-10	7429-90-5
Metal Oxide (proprietary)	20-50	Confidential
Polyvinylidene Fluoride (PVDF)	<5	24937-79-9
Copper Foil	2-10	7440-50-8
Carbon (proprietary)	10-30	7440-44-0
Electrolyte (proprietary)	10-20	Confidential
Carboxymethyl Cellulose (CMC)	<2	9085-26-1
Styrene butadiene rubber (SBR)	<2	9003-55-8
Aluminum and inert materials	Remainder	N/A

3. HAZARDS IDENTIFICATION

PRIMARY ROUTES OF ENTRY

Skin contact, Skin absorption, Eye contact, Inhalation, and Ingestion : NO

SYMPTOMS OF EXPOSURE

Skin contact

No effect under routine handling and use.

Skin absorption

No effect under routine handling and use.

Eye contact

No effect under routine handling and use.

Inhalation

No effect under routine handling and use.

REPORTED AS CARCINOGEN

Not applicable

4. FIRST AID MEASURES

INHALATION, EYE CONTACT, and SKIN CONTACT : Not a health hazard.

INGESTION

If swallowed, obtain medical attention immediately.

If exposure to internal materials within battery due to damaged outer casing, the following actions are recommended.

INHALATION

Leave area immediately and seek medical attention.

EYE CONTACT

Rinse eyes with water for 15 minutes and seek medical attention.

SKIN CONTACT

Wash area thoroughly with soap and water and seek medical attention.

INGESTION

Drink milk/water and induce vomiting; seek medical attention.

5. FIRE FIGHTING MEASURES

GENERAL HAZARD

Battery is not flammable but internal organic material will burn if the battery is incinerated. Combustion products include, but are not limited to hydrogen fluoride, carbon monoxide and carbon dioxide.

EXTINGUISHING MEDIA

Use extinguishing media suitable for the materials that are burning.

SPECIAL FIREFIGHTING INSTRUCTIONS

If possible, remove battery from fire fighting area. If heated above 120°C, battery can explode/vent.

FIREFIGHTING EQUIPMENT

Use NIOSH/MSHA approved full-face self-contained breathing apparatus (SCBA) with full protective gear.

6. ACCIDENTAL RELEASE MEASURES

ON LAND

Place material into suitable containers and call local fire/police department.

IN WATER

If possible, remove from water and call local fire/police department.

7. HANDLING AND STORAGE

HANDLING

No special protective clothing required for handling individual batteries.

STORAGE

Store in a cool, dry place.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

ENGINEERING CONTROLS

Keep away from heat and open flame. Store in a cool dry place.

PERSONAL PROTECTION

Respirator: Not required during normal operations. SCBA required in the event of a fire.

Eye/face protection: Not required beyond safety practices of employer.

Gloves: Not required for handling of batteries.

Foot protection: Steel toed shoes recommended for large container handling.

9. PHYSICAL AND CHEMICAL PROPERTIES

State	Solid
Odor	N/A
PH	N/A
Vapor pressure	N/A
Vapor density	N/A
Boiling point	N/A
Solubility in water	Insoluble
Specific gravity	N/A
Density	N/A

10. STABILITY AND REACTIVITY

REACTIVITY

None

INCOMPATIBILITIES

None during normal operation. Avoid exposure to heat, open flame, and corrosives.

HAZARDOUS DECOMPOSITION PRODUCTS

None during normal operating conditions. If batteries are opened, hydrogen fluoride and carbon monoxide may be released.

CONDITIONS TO AVOID

Avoid exposure to heat and open flame. Do not puncture, crush or incinerate.

11. TOXICOLOGICAL INFORMATION

This product does not elicit toxicological properties during routine handling and use.

Sensitization: NO	Teratogenicity: NO	Reproductive toxicity: NO	Acute toxicity: NO
----------------------	-----------------------	------------------------------	-----------------------

This product does not contain any kinds of the following substances and halogen-type flame retardants including Chlorine and Bromide type harmful flame retardants which are listed in Appendix of TCO documents and relevant international ECO requirements:

Polybromated Biphenyls (PBB)
Polybromated Biphenyl Ethers (PBBE)

Polybromated Biphenyl Oxides (PBBO)
Polybromated Diphenylethers (PBDE)
Polychlorinated Biphenyl (PCB)
Polychlorinated Diphenylethers (PCDE)
Tetrabromophenol A (TBBPA)
Asbestos, Antimonytrioxide, Dioxine

None of the following substances will be exposed, leaked, or emitted during transportation, storage or any operation and any temperature condition:

Chlorinated Fluorohydrocarbon (FCKW)
Acrylonitrile
Styrol
Phenol
Benzol
Mercury of greater than 0.0001 wt% for alkaline battery
Mercury of greater than 0.0005 wt% for other battery
Lithium content of greater than 0.5g/battery
Cadmium, lead, and other harmful heavy metal

And will comply with the regulation of 49 CFR (DOT regulation), International Air Transport Association (IATA), and Deuche Forschungsgemeinschaft (DFG) regarding concentrations of emitted substances.

This product does not contain mercury and lithium-metal.

Mercury content: <

Lithium-metal content: <

If the batteries are opened through misuse or damage, discard immediately. Internal components of battery are irritants and sensitizers.

12. ECOLOGICAL INFORMATION

Some materials within the battery are bioaccumulative. Under normal conditions, these materials are contained and pose no risk to persons or the surrounding environment.

13. DISPOSAL INFORMATION

Recommended methods for safe and environmentally preferred disposal :

Product(waste from residues)

Do not throw out a used battery. Recycle it through the recycling company.

Contaminated packaging

Neither a container nor packing is contaminated during normal use. When internal materials leaked from a battery contaminates, dispose as industrial wastes subject to special control.

RCRA Waste Code: Nonregulated

Dispose of according to all federal, state, and local regulations.

14. TRANSPORTATION INFORMATION

Lishen' BL-5C (1020mAh) Lithium-Ion batteries are considered to be "Rechargeable Lithium Ion Prismatic Batteries" and meet the requirements of transportation by the International: Civil Aviation Organization (ICAO) Technical Instructions (2014-2015 Edition), the International Air Transport Association (IATA) Dangerous Goods Regulation (DGR) 56th Edition 2015 Packing instruction 965 Section IB or II for Lithium Ion battery, the International Maritime Dangerous Goods (IMDG) Code (2010 Edition) with special provision 188 & 230, US Hazardous Materials Regulations 49 CFR(Code of Federal Regulations)Sections 173-185 Lithium batteries and cells. the UN Recommendations on the Transport of Dangerous Goods, Manual of Tests and Criteria 38.3 Lithium batteries, 4th revised edition(UN3480) as "non-dangerous goods" or "non-hazardous materials". The mentioned batteries are complied with the special provision, Section I of PI965 to PI967. These lithium batteries can be transported in nonrestrictive material and as Non-Dangerous Goods as they meet all the requirements in below:

1、Lithium content requirement

- 1.1** For the bar cells, the lithium content can not overpass 20Wt/h;
- 1.2** For the batteries, the lithium content can not overpass 100Wt/h;

2 Meet with UN Test Requirement

- 2.1** All the cell and battery must be verified to meet with all the requirements in Part 3 -38.3 item (UN38.3 tests) for "Recommendations on the Transport of Dangerous Goods, Manual of Tests and Criteria".

3 Package Requirement

- 3.1** The cell and battery must be packaged specially and singly, and put into hard outer package to prevent short-circuit if they do not be assembled in finished equipments (such as mobile phone, camera, NBPC. and so on)
- 3.2** The cell quantity is more than 24pcs or the battery quantity is more than 12pcs, they must be asked to meet with the requirements in blow besides they are assembled in finished equipment.
 - a** Every package must be marked in the content that the packages are loaded in lithium cells or batteries, also add new lithium iron operation label , also need point out the corrective actions when the packages are damaged.
 - b** Every batch shipment must be appendixes document which should contain the content that the packages are loaded in lithium cells or batteries, also need point out the corrective actions when the packages are damaged.
 - c** Every package must pass 1.2mm fall test in any direction. No damage for the cells and batteries, no move and touch together, no cells or batteries escape from the package.
 - d** Every package weight can not overpass 10kg if the batteries can not be assembled in finished equipment.

The information and recommendations set forth are made in good faith and believed to be accurate as of the date of preparation. Tianjin Lishen Battery Co. Ltd. makes no warranty, expressed or implied, with respect to this information and disclaims all liabilities from reliance on it

Test results of the UN Recommendation on the Transport of Dangerous Goods

Manual of Test and Criteria (38.3 Lithium battery)		Test Results	Remark
No	Test item	Pass	
T1	Altitude Simulation	Pass	
T2	Thermal Test	Pass	
T3	Vibration	Pass	
T4	Shock	Pass	
T5	External Short Circuit	Pass	
T6	Impact	Pass	
T7	Overcharge	Pass	For pack only
T8	Forced Discharge	Pass	For cell only

15. REGULATORY INFORMATION

OSHA hazard communication standard (29 CFR 1910.1200)

Hazardous Non-hazardous

16. OTHER INFORMATION

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide.

First Edition : 2016-12-19 Latest Edition: 2016-12-19

Prepared and Approved By
TianJin Lishen Battery Company
R&D Center

The information and recommendations set forth are made in good faith and believed to be accurate as of the date of preparation. Tianjin Lishen Battery Co. Ltd. makes no warranty, expressed or implied, with respect to this information and disclaims all liabilities from reliance on it