

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** OSRAM

**Supplier's address:** LEDVANCE GmbH, Parkring 33, Garching, Germany

**Model identifier:** AC34227

## Type of light source:

|                                                     |        |                                 |      |
|-----------------------------------------------------|--------|---------------------------------|------|
| Lighting technology used:                           | CFLni  | Non-directional or directional: | NDLS |
| Light source cap-type (or other electric interface) | G24q-3 |                                 |      |
| Mains or non-mains:                                 | NMLS   | Connected light source (CLS):   | No   |
| Colour-tuneable light source:                       | No     | Envelope:                       | -    |
| High luminance light source:                        | No     |                                 |      |
| Anti-glare shield:                                  | No     | Dimmable:                       | Yes  |

## Product parameters

| Parameter                                                                                                                                             | Value                  | Parameter                                                                                                                                                  | Value                  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| <b>General product parameters:</b>                                                                                                                    |                        |                                                                                                                                                            |                        |
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer                                                                         | 28                     | Energy efficiency class                                                                                                                                    | G                      |
| Useful luminous flux ( $\phi_{\text{use}}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 1 600 in Sphere (360°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 6 500                  |
| On-mode power ( $P_{\text{on}}$ ), expressed in W                                                                                                     | 27,3                   | Standby power ( $P_{\text{sb}}$ ), expressed in W and rounded to the second decimal                                                                        | 0,00                   |
| Networked standby power ( $P_{\text{net}}$ ) for CLS, expressed in W and rounded to the second decimal                                                | -                      | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set                                                         | 80                     |
| Outer dimensions without                                                                                                                              | Height                 | Spectral power distribution in the                                                                                                                         | See image in last page |
|                                                                                                                                                       | Width                  |                                                                                                                                                            |                        |
|                                                                                                                                                       | Depth                  |                                                                                                                                                            |                        |

|                                                                                                   |   |  |                                      |       |
|---------------------------------------------------------------------------------------------------|---|--|--------------------------------------|-------|
| separate control gear, lighting control parts and non-lighting control parts, if any (millimetre) |   |  | range 250 nm to 800 nm, at full-load |       |
| Claim of equivalent power <sup>(a)</sup>                                                          | - |  | If yes, equivalent power (W)         | -     |
|                                                                                                   |   |  | Chromaticity coordinates (x and y)   | 0,313 |

(a) - : not applicable;

(b) - : not applicable;

