


Masse im Steckbereich nach
DIN46342, Teil 1







Dimensions zone
d'emboîtement selon
DIN46342, partie 1







Dimensions in the tab sector
DIN46342, part 1

Werkstoff/Matière/Material
.2 = Bronze/bronze
.6 = Messing/laiton/brass

■ = Oberflächen/Surface/Surface-plating
Seite/page/page 5.011



						
Artikelnummer Numéro d'article Part-No.	3780s08.2	03780s08.2	3773a05.2	03773a05.2	3773a05.6	03773a05.6
Bohrung/Trou/Hole	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3
T	1.9	1.9	3.2	3.2	3.2	3.2
L	11	11	7.1	7.1	7.1	7.1
L1	12.9	12.9	12.2	12.2	12.2	12.2
B1	2.8	2.8	3.8	3.8	3.8	3.8
B2	2.8	2.8	2.8	2.8	2.8	2.8
∅D	1.3	1.3	1.2x3	1.2x3	1.2x3	1.2x3
B	1.3	1.3	1.4	1.4	1.4	1.4
S	0.8	0.8	0.5	0.5	0.5	0.5
Werkzeuge Outils Toolings	18	1041s08	17	104805	17	104805

						
Artikelnummer Numéro d'article Part-No.	3775a05.2	03775a05.2	3775a05.6	03775a05.6	3773a08.6	03773a08.6
Bohrung/Trou/Hole	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3
T	3.2	3.2	3.2	3.2	3.2	3.2
L	7.1	7.1	7.1	7.1	7.1	7.1
L1	12.2	12.2	12.2	12.2	12.2	12.2
B1	3.8	3.8	3.8	3.8	3.8	3.8
B2	2.8	2.8	2.8	2.8	2.8	2.8
∅D	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	1.2x3	∅ 1.3
B	1.4	1.4	1.4	1.4	1.4	1.4
S	0.5	0.5	0.5	0.5	0.8	0.8
Werkzeuge Outils Toolings	17	104805	17	104805	18	104808