

Technische Daten

Typ	Best-Nr.	Zulässige Belastung kg	Bauhöhe A mm	Höhenverstellung B mm	Zwischenstellung mm	Endhöhe C mm	Auflage-decke IF mm	Fuß-abstand D mm	Fuß-abstand E mm	Gewicht kg
AB 1,5-260	801.329.2	1500	260	145	35	405	70	255	220	2,2
AB 1,5-420	801.330.6	1500	425	240	65	665	70	400	350	3,6
AB 1,5-1200	803.639.0	1500	1200	800	80	2000	130	750	660	16,5
AB 3-320	801.331.4	3000	320	210	50	530	75	320	285	3,8
AB 3-1200	803.640.3	3000	1200	800	80	2000	130	750	660	20,0
AB 5-365	801.332.2	5000	380	200	50	580	70	370	370	6,4
AB 8-360	801.333.0	8000	380	215	55	595	125	400	400	10,5
AB 8-580	801.334.9	8000	580	370	75	950	125	600	600	15,4
AB 16-290	803.173.8	16000	290	165	70	455	130	250	250	15
AB 16-440	803.174.6	16000	440	285	70	725	130	400	400	21
AB 16-675	803.175.4	16000	675	450	70	1125	130	450	450	25
AB 5-230-S	803.176.2	5000	230	90	--	320	75	190	190	5
AB 12-320-S	803.177.0	12000	320	165	--	485	125	220	220	10
AB 12-450-S	802.742.0	12000	450	275	--	725	125	350	350	14
AB 8-345-SH	803.179.7	8000	360	245	--	605	130	400	400	13
AB 8-950-SH	804.400.7	8000	950	500	--	1450	140	650	650	35
AB 8-1400-SH	804.397.3	8000	1400	700	--	2100	140	850	850	45

