


# Steckzungen 6,3 mm Languettes plates Mounting tabs

Werkstoff/Matière/ Material  
 .2 = Bronze/bronze  
 .4 = Kupfer/cuivre/copper  
 .6 = Messing/laiton/brass






■ = Oberflächen/Surface/Surface-plating  
 Seite/page/page 5.011



## Masse im Steckbereich DIN46342, Teil 1

## Dimensions zone d'emboîtement selon DIN46342, partie 1

## Dimensions in the tab sector DIN46342, part1



Artikelnummer  
Numéro d'article  
Part-No.

Bohrung/Trou/Hole

**3867ab.6**

∅ 1  
T 2.9  
H 14.2  
A 5  
B1 8.5  
L1 18  
L 9.5  
∅D 1.65  
B 1  
S 0.8

**03867ab.6**

∅ 1  
T 2.9  
H 14.2  
A 5  
B1 8.5  
L1 18  
L 9.5  
∅D 1.65  
B 1  
S 0.8

**38671.6**

∅ 1.1  
T 3  
H 13.2  
A 5  
B1 8  
L1 18  
L 10  
∅D 3  
B 1  
S 0.8

**038671.6**

∅ 1.1  
T 3  
H 13.2  
A 5  
B1 8  
L1 18  
L 10  
∅D 3  
B 1  
S 0.8

**3867d.2**

∅ 1.1  
T 3  
H 9.3  
A 5  
B1 6  
L1 20  
L 14  
∅D 1.65  
B 1  
S 0.8

Werkzeuge  
Outils  
Toolings






**24**

**1046ab**

**28**

**1047r**

**33**



Artikelnummer  
Numéro d'article  
Part-No.

Bohrung/Trou/Hole

**3867d.6**

∅ 1.1  
T 3  
H 9.3  
A 5  
B1 6  
L1 20  
L 14  
∅D 1.65  
B 1  
S 0.8

**03867d.6**

∅ 1.1  
T 3  
H 9.3  
A 5  
B1 6  
L1 20  
L 14  
∅D 1.65  
B 1  
S 0.8

**3867d1.6**

∅ 1.1  
T 3  
H 9.3  
A 5  
B1 6  
L1 21.5  
L 15.5  
∅D 1.65  
B 1  
S 0.8

**03867d1.6**

∅ 1.1  
T 3  
H 9.3  
A 5  
B1 6  
L1 21.5  
L 15.5  
∅D 1.65  
B 1  
S 0.8

**3867c.6**

∅ 1.1  
T 3.2  
H 8  
A 5  
B1 6  
L1 18  
L 12  
∅D 1.65  
B 1  
S 0.8

Werkzeuge  
Outils  
Toolings

**33**

**1046d**

**33**

**1046d1**

**26**