


Steckzungen 6,3 mm Languettes plates Mounting tabs

Werkstoff/Matière/Material
 .2 = Bronze/bronze
 .4 = Kupfer/cuivre/copper
 .6 = Messing/laiton/brass






■ = Oberflächen/Surface/Surface-plating
 Seite/page/page 5.011









Masse im Steckbereich
DIN46342, Teil 1

Dimensions zone
d'emboîtement selon
DIN46342, partie 1

Dimensions in the tab sector
DIN46342, part 1

					
Artikelnummer Numéro d'article Part-No.	3868y.6	3867b.2	03867b.2	3867b.6	03867b.6
Bohrung/Trou/Hole	∅ 1.2	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3
T	3.5	3	3	3	3
H	13.5	12	12	12	12
A	5	5	5	5	5
B1	8	8	8	8	8
L1	21.5	16.2	16.2	16.2	16.2
L	13.5	8.2	8.2	8.2	8.2
∅D	1.65	1.65	1.65	1.65	1.65
B	1.1	1.3	1.3	1.3	1.3
S	0.8	0.8	0.8	0.8	0.8
Werkzeuge Outils Toolings	28	28	1046b	28	1046b

						
Artikelnummer Numéro d'article Part-No.	3868a.6	03868a.6	3867e.6	03867e.6	3867k.6	03867k.6
Bohrung/Trou/Hole	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.35	∅ 1.35
T	3.5	3.5	4	4	3.5	3.5
H	11.1	11.1	13	13	12.5	12.5
A	5	5	5	5	5	5
B1	6.9	6.9	7	7	8	8
L1	16	16	16	16	16.2	16.2
L	9.1	9.1	9	9	8.2	8.2
∅D	1.65	1.65	1.65	1.65	1.65	1.65
B	1.3	1.3	1.3	1.3	1.3	1.3
S	0.8	0.8	0.8	0.8	0.8	0.8
Werkzeuge Outils Toolings	28	1046a	28	1046e	28	1046k