








Steckzungen 2,8 mm Languettes plates Mounting tabs

					
Artikelnummer Numéro d'article Part-No.	3773e05.2	3775b08.6	03775b08.6	3779wr.2	3779u.2
Bohrung/Trou/Hole	∅ 1.4	∅ 1.45	∅ 1.45	∅ 1.5	∅ 1.55
T	3.2	7	7	4.3	4.3
L	7	7	7	6.8	6.8
L1	12.3	16.1	16.1	12.5	12.5
B1	3.8	3.9	3.9	5	7.2
B2	2.8	2.8	2.8	2.8	2.8
∅D		1.3	1.3	1.2	1.2
B	1.5	1.4	1.4	1.5	1.55
S	0.5	0.8	0.8	0.5	0.5
Werkzeuge Outils Toolings	17	18	104808	13	17

Werkstoff/Matière/Material
.2 = Bronze/bronze
.6 = Messing/laiton/brass








= Oberflächen/Surface/Surface-plating
Seite/page/page 5.011



Masse im Steckbereich nach DIN46342, Teil 1

Dimensions zone d'emboîtement selon DIN46342, partie 1

Dimensions in the tab sector DIN46342, part 1

							
Artikelnummer Numéro d'article Part-No.	3785s.6	3776b.6	3785y05.6	3785h.6	03785h.6	3785q05.6	03785q05.6
Bohrung/Trou/Hole	∅ 0.8	∅ 0.9	∅ 0.9	∅ 0.9	∅ 0.9	∅ 0.9	∅ 0.9
T	3.5	2.5	2.5	3.5	3.5	3.5	3.5
L	8.1	6.5	10	8.1	8.1	10	10
L1	15.4	12.8	14.5	15.4	15.4	16.9	16.9
B1	8	4	5.2	8	8	5.2	5.2
A	4	2.5	2.5	4	4	2.5	2.5
∅D	1.3		1.3	1.3	1.3	1.3	1.3
B	0.65	0.9	0.8	0.8	0.8	0.8	0.8
S	0.8	0.5	0.5	0.8	0.8	0.5	0.5
Werkzeuge Outils Toolings	32	93	64	32	1046h	64	1051q05