

# Steckzungen 6,3 mm Languettes plates Mounting tabs



Masse im Steckbereich  
DIN46342, Teil 1







Dimensions zone  
d'emboîtement selon  
DIN46342, partie 1







Dimensions in the tab sector  
DIN46342, part1

Werkstoff/Matière/Material  
.2 = Bronze/bronze  
.6 = Messing/laiton/brass  
.7 = Neusilber/mailechort/german silver  
.9 = Stahl/acier/steel

■ = Oberflächen/Surface/Surface-plating  
Seite/page/page 5.011



						
Artikelnummer Numéro d'article Part-No.	<b>3865l.6</b>	<b>03865l.6</b>	<b>3865m.6</b>	<b>3866m.6</b>	<b>03866m.6</b>	<b>3867m.6</b>
Bohrung/Trou/Hole	Ø 1.5	Ø 1.5	Ø 1.5	Ø 1.5	Ø 1.5	Ø 1.5
T	3	3	3	3	3	3
L	17	17	17	20	20	20
L1	20	20	20	23	23	23
B1	6.3	6.3	6.3	6.3	6.3	6.3
A	4	4	4	4	4	4
øD	1.65	1.65		1.65	1.65	
B	1.5	1.5	1.5	1.5	1.5	1.5
S	0.8	0.8	0.8	0.8	0.8	0.8
Werkzeuge Outils Toolings	<b>38</b>	<b>1046l</b>	<b>38</b>	<b>38</b>	<b>1046m</b>	<b>38</b>

						
Artikelnummer Numéro d'article Part-No.	<b>3865q.6</b>	<b>03865q.6</b>	<b>3865p.6</b>	<b>03865p.6</b>	<b>3866s.2</b>	<b>03866s.2</b>
Bohrung/Trou/Hole	Ø 1.5	Ø 1.5	Ø 1.5	Ø 1.5	Ø 1.5	Ø 1.5
T	4	4	4	4	6	6
L	15	15	26.5	26.5	8.2	8.2
L1	20.5	20.5	32	32	16	16
B1	8	8	8	8	8	8
A	5	5	5	5	5	5
øD	1.65	1.65	1.15	1.15	1.8	1.8
B	1.425	1.425	1.425	1.425	1.45	1.45
S	0.8	0.8	0.8	0.8	0.8	0.8
Werkzeuge Outils Toolings	<b>23</b>	<b>1047q</b>	<b>38</b>	<b>1048p</b>	<b>23</b>	<b>1046s</b>