





## Frontseitig aufschraubbare Überspannungsbegrenzer Kompaktschütze CWC07-CWC025

Bild	verwendbar für	Schaltbild	Spannung	Typ	Gewicht g
	CWC07-025 + CWCA0  CWC07-016 + CWCA0		12-24 V 50/60Hz 24-48 V 50/60Hz 50-127 V 50/60Hz 130-250 V 50/60Hz 275-380 V 50/60Hz 400-510 V 50/60Hz  180-230V 50/60Hz (empfohlen in Stromkreisen mit Restströmen > 1,4 mA)	<b>RCC0-1 D49</b> <b>RCC0-2 D53</b> <b>RCC0-3 D55</b> <b>RCC0-4 D63</b> <b>RCC0-5 D84</b> <b>RCC0-6 D73</b>  <b>RCAC0 D87</b>	8
	CWC07-025 + CWCA0		12-48V 50/60Hz/12-60VDC 50-127 V 50/60Hz/60-180VDC 130-275 V 50/60Hz/180-300VDC 277-380 V 50/60Hz/300-510VDC 400-510 V 50/60Hz	<b>VRC0-1 E01</b> <b>VRC0-2 E34</b> <b>VRC0-3 E38</b> <b>VRC0-4 E41</b> <b>VRC0-4 D73</b>	8
	CWC07-016 + CWCA0		12-600VDC  Zenerdiode 12-250VDC	<b>DIC0-1 C33</b>  <b>DIZC0 C26</b>	8