Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: XENOTEC

Supplier's address: Kundendienst, Saffiger Straße 14, 56299 Ochtendung, DE

Model identifier: PE-BM85

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	Verlötet		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Yes

Product parameters			
Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	4	Energy efficiency class	G
Useful luminous flux (ϕuse), indicating if it refers to the flux in a sphere (360º), in a wide cone (120º) or in a narrow cone (90º)	300 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	2900...3100
On-mode power (P_{on}), expressed in W	3,5	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,35
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	70
Outer dimensions without separate control gear, lighting control	Height	850	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
	Width	600		
	Depth	600		

parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power[a]	-	If yes, equivalent power (W)	-	
		Chromaticity coordinates (x and y)	0,450 0,400	
Parameters for LED and OLED light sources:				
R9 colour rendering index value	5	Survival factor	1,00	
the lumen maintenance factor	0,90			

[a]'-' : not applicable;

[b]'-' : not applicable;

Spectral Ratio: R=43.8%,G=44.1%,B=12.1%,