


Pin Hole Layout  
(Jack Bottom View)

6.	Cover	PBT+30% Fibre Glass	1	Black Color
5.	Housing	PBT+30% Fibre Glass	1	Black Color
4.	Pin(2.5 $\varnothing$ )	Copper	1	Nickel Plated
3.	Break Terminal	0.4T Brass	1	Silver Plated
2.	Sleeve Spring	0.2T Phosphor Bronze	1	Silver Plated
1.	Pin Terminal	0.4T Brass	1	Silver Plated
NO.	Description	Material	Q'TY	Finish



**SPECIFICATIONS:**  
 Contact Resistance : 30m $\Omega$  max  
 Current Rating : Max 24VDC/5A  
 Insulation Resistance : 100M $\Omega$  min. at DC 500V  
 Dielectric Withstand Voltage : AC 500V for one minute  
 Remark: ▲ : The Most Important Dimension

Artikelnummer Artikeltext

072819 DC-Einbaubuchse, Schalter in Ruhestellung geschl., verschließbar, Winkelkontakte, Stift 2,5 mm

BKL - ELECTRONIC Kreimendahl GmbH

~ Markenstück 14 ~ 58509 Lüdenscheid

Telefon +49(0)2351/3621-0

~ Telefax +49(0)02351/3621-29

~ E-Mail: info@bkl-electronic.de

~ www.bkl-electronic.de