

KERN MWS 300K-1LM



Stretcher scale with low overall height for easy access – with approval for medical use and optionally with verification



Category	
Brand	KERN
Product category	Medical scale
Product group	Stretcher Scale
Product family	MWS-L

Measuring System	
Weighing system	Strain gauge
Weighing capacity [Max]	300 kg
Readability [d]	0,1 kg
Reproducibility	0,1 kg
Linearity	± 0,1 kg
Minimum weight [Min]	2 kg
Conformity assessment possible	✓
Resolution	3.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	300 kg (M1)
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,1 kg
Construction type of the scale	Single-range balance
Units	kg
Default unit	kg

Display	
Display type	LCD
Display digit height	25 mm
Languages of the user interface	Symbol language

Construction	
Dimension housing (W×D×H)	1500×860×68 mm
Dimensions completely mounted (W×D×H)	1506×920×68 mm
Dimension display device (W×D×H)	210×110×50 mm

Dimensions weighing surface (W×D)	800×1200 mm
Dimensions weighing surface	800×1200 mm
Dimensions weighing platform (W×D×H)	1196×797×68 mm
Material housing	steel, lacquered
Material weighing plate	steel, lacquered
Material display housing	plastic
Level indicator	✓
Levelling feet adjustable	✓
Wall mount	✓
Transport wheels	✓
Cable length	1,8 m
Display device cable length	2 m
Load cells - number	4

Functions	
PreTare function	✓
Function for averaging under unstable weighing conditions	✓
Function for BMI calculation	✓
Hold function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 4 min 5 min 2 min
Tare function	manual (multi)
Number of keys for operation	20

Interface	
Interfaces	RS-232 standard

Power Supply	
Supplied power supply	Power supply & battery function (battery not included)
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 500 mA

KERN MWS 300K-1LM

KERN

Stretcher scale with low overall height for easy access – with approval for medical use and optionally with verification

Power socket for mains adapter	Hollow plug, inside minus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
Battery / accumulator type	NiMH
Battery	6×1.5 V AA
Battery operating time	50 h
Rechargeable battery	FOB-A08
Rechargeable battery operating time - backlight off	45 h
Rechargeable battery charging time	14 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	0,1 kg
Approval in accordance with 2017/745 (MDR, med.)	✓

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-129
Article number for DAkkS calibration	963-129
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	1650×1008×123 mm
Shipping method	Freight
Net weight approx.	42 kg
Gross weight approx.	55 kg
Shipping weight	55 kg

Product information

GTIN/EAN number	4045761192881
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



FACTORY

