

KERN PNJ 600-3M

The new standard in the laboratory with robust tuning fork weighing system, with optional verification



Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PNJ

Measuring System

Weighing system	Tuning fork
Weighing capacity [Max]	620 g
Readability [d]	0,001 g
Reproducibility	0,001 g
Linearity	± 0,004 g
Minimum weight [Min]	0,02 g
Conformity assessment possible	✓
Resolution	620.000
Tare range	620 g
Adjustment options	Internal calibration (automatic)
Stabilization time	3 s
Warm-up time	4 h
Eccentric loading at 1/3 [Max]	0,004 g
Units (if device is conformity assessed)	g ct
Minimum weight [Min] (ct)	0,2 ct
USP Minimum weight of sample (k = 2, U = 0.1%)	2 g
Construction type of the scale	Single-range balance

Units

g
gn
dwt
tl (Tw)
tl (HK)
ozt

tl (Singap, Malays)
ct
mo
lb
oz
tol

Weighing capacity [Max] (ct)	3100 ct
Readability carat [d] (ct)	0,01 ct
Default unit	g

Display

Display type	LCD
Display type	LCD
Display backlight	✓
Display screen size	109×27 mm
Display digit height	16,5 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	196×293×266 mm
Dimensions completely mounted (W×D×H)	196×293×266 mm
Dimensions rectangular draught shield - inner (W×D×H)	172×171×160 mm
Dimensions weighing surface (Ø)	140 mm
Dimensions weighing surface	140 mm
Material housing	plastic
Material weighing plate	stainless steel
Material draught shield	glass
Level indicator	✓
Levelling feet adjustable	✓

Functions

Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Capacity - Display	✓
Counting function	✓
Counting resolution (laboratory conditions)	620.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Reference quantity	10, 30, 50, 100
IP protection - display	no IP protection
IP protection - platform	no IP protection

KERN PNJ 600-3M

KERN

The new standard in the laboratory with robust tuning fork weighing system, with optional verification

Tare function	manual (multi)
Number of keys for operation	5

Interface	
Interfaces	RS-232 standard

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
	UK
	US
	CH

Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US
	CH

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
--	-------------------------

Input voltage device / power [Max]	5,95 V, 1 A
------------------------------------	-------------

Power socket for mains adapter	Hollow plug, inside plus, Ø outside 4,75 mm, Ø inside 1,7 mm, long 9,5 mm
--------------------------------	---

Battery voltage	3 V
-----------------	-----

Battery - Individual weight	6,6 g
-----------------------------	-------

Environmental conditions

Ambient temperature [Min]	5 °C
---------------------------	------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Max]	80 %
-------------------------------	------

Approval

CE mark	✓
---------	---

Conformity assessment possible ex works	✓
---	---

Accuracy classe	II
-----------------	----

Verification scale interval [e]	0,01 g
---------------------------------	--------

Verification scale interval [e] (ct)	0,1 ct
--------------------------------------	--------

Services (optional)

Article number for conformity assessment	965-216
--	---------

Article number for DAkkS calibration	963-103
--------------------------------------	---------

Article number for certificate of conformity	969-517
--	---------

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	409×320×318 mm
------------------------------	----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	4,2 kg
--------------------	--------

Gross weight approx.	6 kg
----------------------	------

Shipping weight	8,3 kg
-----------------	--------

Product information

GTIN/EAN number	4045761179882
-----------------	---------------

REACH classification	no prohibited substances
----------------------	--------------------------

Pictograms

STANDARD



OPTION



FACTORY

