

KERN OZP 552

KERN

Individuality, variety and flexible working through our modular construction system ► Stereo microscope heads



Category

Brand	Optics
Product category	Microscope
Product group	Stereo Microscope-Head
Product family	OZB-M

Construction

Optical system	Greenough
Tube type	Trinocular
Tube angle of inclination	35°
Tube 360° rotation	✓
Light distribution	0:100
Interpupillary distance [Min]	52 mm
Interpupillary distance [Max]	76 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-6
Diopter adjustment [Max]	6

Ocular

Ocular type	Eyepiece HSWF 10x / Ø 23mm with anti-fungus, high eye point
Ocular field width	HSWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	23 mm
Ocular diameter	30 mm

Objective

Objectives magnifications	0,6x - 5,5x
---------------------------	-------------

Focussing

Field of view [Min]	38,3 mm
Field of view [Max]	4,2 mm
Standard total magnification [Min]	6x
Standard total magnification [Max]	55x
Zoom [Min]	0,6x
Zoom [Max]	5,5x
Sample height [Max]	110 mm
Working distance	108 mm
Magnification ratio	9,2:1

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	345×300×220 mm
Shipping method	Parcel service
Net weight approx.	2,6 kg
Gross weight approx.	3,0 kg
Shipping weight	4,6 kg

Product information

GTIN/EAN number	4045761183650
REACH classification	no prohibited substances

Pictograms

STANDARD

