





### First-class professional Class I, Class II sound level meter



Data logging function with date and time in the device...



... and data transfer using MicroSD (4G) memory card (included in delivery), RS-232 or USB




Different sound pressure levels can be selected, such as, LAeq, LcPeak, LaF, LaFMax, LaFMin, SD, SEL, E



**Features**

- Ideal for measurements for workplaces outdoor, e.g. at airports, on building sites, in road traffic etc. with wide frequency access
- Modern microcontroller architecture for increased stability and accuracy
- A specially-developed algorithm permits a compliant dynamic range of more than 120 dB! (SW 1000: > 123 dB; SW 2000: > 122 dB)
- Three profiles and 14 user-defined measurements can be calculated in parallel with different frequency and time weighting
- LN statistics and display of the graph showing the progression of time
- User-defined integral interval measurement up to a maximum of 24 hours is possible
- Frequency weighting (filter) A, B, C, Z
- Time interval during measurement: F (fast), S (slow), I (pulse)

- Freely-definable limits for the output of an optical alarm signal
- Peak Hold function to capture peak value
- Octave function for targeted sound analysis, can be expanded to 1/3 octave through the purchase of a licence
- TRACK function with graphic display of a measurement
- Calibration mode (with optional calibrator)
- Trigger mode: external start/stop of measurement via 3,5 mm connector
- Automatic measurement for timer function is possible
- Operating languages: EN, DE, FR, ES, PT
- Option of fitting a stand on the rear of the housing, 1/4" thread
-  Delivery in robust transport case

Discover more details and matching accessories online!

**Technical data**

- Applicable standards:
  - IEC61672-1:2014-07
  - GB/T3785.1-2010
  - 1/1 Octave in accordance with IEC 61260:2014
- 1/2" microphone
- Output (direct or alternating current) AC (max 5 VRMS), DC (10 mV/DB)
- Mains adapter external, standard
- Battery operation possible, 4x1.5 V AA not included, operating time up to 10 h
- Permissible ambient temperature -10 °C/50 °C
- Overall dimensions WxDxH 200x85x40 mm
- Net weight approx. 0,40 kg

STANDARD



OPTION



Model	Accuracy class	Measuring range linear [Min]-[Max] dB	Readout [d] dB	Frequency range [Min]-[Max] kHz	Sensitivity mv/Pa	Option
						Factory calibration certificate
<b>SAUTER</b>						KERN
<b>SW 1000</b>	Class 1	20 - 134	0,1	0,01 - 20	50	961-281
<b>SW 2000</b>	Class 2	25 - 136	0,1	0,02 - 12,5	40	961-281