




Welle / shaft: Stereo / dual turn  
 Ø 6 mm, L = 15 mm gezahnt (18 Zähne)  
 Buchse / bushing M7 x 0,75  
 Drehbereich / rotation angle: 300° ± 5 %  
 Belastbarkeit / rated wattage: lin. 0,2 W / log 0,05 W

Kontakte: SPCC, kalt gewalzter Stahl, vernickelt / Cold rolled steel sheets, nickel plated



ALPHA POT 16 RV16A01F -20

### Order Information

Artikelbez.	Widerstandskurve	Wert
RV16A01F20KB5K	linear	2 x 5 kΩ
RV16A01F20KB10K	linear	2 x 10 kΩ
RV16A01F20KB50K	linear	2 x 50 kΩ
RV16A01F20KB100K	linear	2 x 100 kΩ
RV16A01F20KA5K	logarithmisch	2 x 5 kΩ
RV16A01F20KA10K	logarithmisch	2 x 10 kΩ
RV16A01F20KA50K	logarithmisch	2 x 50 kΩ
RV16A01F20KA100K	logarithmisch	2 x 100 kΩ

