


Datasheet

Item no. 1576707, 1576708, 1576709, 1576710, 1576711, 1576712



Aufbau:
 Glasrohr, durchsichtig
Kontaktkappen:
 Messing, vernickelt

Construction:
 Glass tube, transparent
Contact caps:
 Brass, nickel plated



Bemessungswerte / Ratings

Art.-No.	Strom Current (A)	Spannung Voltage	Ausschaltvermögen Breaking capacity	Spannungsfall Voltage drop Max [mV]	Max. Leistungsverlust Max power dissip. [W]	Schmelzintegral Melting Integral [A ² s]
TC-UL521.010	200 mA	250 V	35 A	1000	0,36	0,18
TC-UL521.014	500 mA	250 V	35 A	529	0,43	1,4
TC-UL521.020	2 A	250 V	100 A	195	0,59	29
TC-UL521.060	3 A	250 V	100 A	172	0,74	82
TC-UL521.024	5 A	125 V	10.000 A	152	1,1	226
TC-UL521.025	6 A	125 V	10.000 A	148	1,3	428

Schmelzzeit-Grenzwert / Pre- arcing time limits

Prüfstrom Testing current	Schmelzzeit / Blow Time	
	Minimum	Maximum
100 %	4 Hrs	N / A
135 %	N / A	1 Hr
200 %	N / A	15 sec
1000 %	10 ms	N / A

Technische Änderungen sind vorbehalten! / Technical data subject to change! 08 / 2017