


DIN 464

Rändelschrauben, hohe Form



Maße	M 3	M 4	M 5	M 6	M 8	M 10
d_k	12	16	20	24	30	36
k	2,5	3,5	4,0	5,0	6,0	8,0
h	5,7	7,64	9,64	11,57	15,57	19,48
d_s	6	8	10	12	16	20