

SAUTER SP 200K

KERN

Compact photometer, optimised for accurate light measurement, including LED light measurement



Category

Brand	Sauter
Product category	Environment/ Occupational safety
Product group	Light measuring instrument
Product family	SP

Measuring System

Measuring head measuring frequency	2 Hz
Measuring range [Max] (Lux)	200 lx; 2000 lx; 20000 lx; 200000 lx
Readability illumination [d] (lx)	0,1 lx; 1 lx; 10 lx; 100 lx
Units	lx fc

Display

Display type	LCD
Display digit height	16 mm

Construction

Dimension housing (W×D×H)	185×68×38 mm
Dimensions completely mounted (W×D×H)	185×68×38 mm
Material housing	plastic
Material display housing	plastic

Functions

Hold function	✓
Peak function	✓

Power Supply

Supplied power supply	Battery
-----------------------	---------

Battery / accumulator type	Alkali(-Manganese)
Battery	9 V block
Battery connection	9V Bloc
Battery operating time	200 h
Battery voltage	9 V
Battery - Number of cells	1
Battery - Individual weight	45,5 g
Battery - Total weight	45,5 g
Battery/Accu connected	not connected, enclosed

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration	961-190
--	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	200×106×55 mm
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,30 kg
Shipping weight	0,28 kg

Product information

GTIN/EAN number	4045761200579
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

