



**intercontec**  
products

# 923 Klemmring mit Knickschutz

TE Teile Nr.: A2-0164-001-000  
IC Ref. Nr.: A2.164.01

## Werkstoff

Klemmring  
Knickschutz

Messing, vernickelt  
PU UL 94/ V0


## Technische Daten

Kabelklemmbereich

bis  $\varnothing 11$  mm

## Einsatzbereich:

923 Stecker und 923 Kupplungen,  
mit Anschlussgewinde M24x1.



## Hauptabmessungen

Klemmring mit Knickschutz

Y6-H208-000-0DE erstellt: 20.08.2018/MHu

© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) und speedtec sind Marken.

Auch wenn TE Connectivity (TE) bemüht ist, die Korrektheit der Informationen in diesem Beitrag sicherzustellen, übernimmt TE keinerlei Gewährleistung dafür, dass diese fehlerfrei, zutreffend, korrekt, verlässlich oder aktuell sind. TE behält sich das Recht vor, die in diesem Beitrag genannten Informationen jederzeit ohne Ankündigung zu ändern. TE weist ausdrücklich jegliche Gewährleistung hinsichtlich der in diesem Beitrag genannten Informationen zurück, einschließlich der implizierten Gewährleistung der Marktgängigkeit oder Eignung für bestimmte Zwecke. Die Maßangaben in diesem Beitrag dienen ausschließlich zu Referenzzwecken und Änderungen sind vorbehalten. Änderungen der Spezifikationen sind vorbehalten. Bitte fragen Sie TE nach den aktuellen Maßangaben und Designspezifikationen

TE Connectivity Industrial GmbH  
Bernrieder Straße 15  
94559 Niederwinkling, Germany  
+49 9962 2002 - 0  
[intercontec@te.com](mailto:intercontec@te.com)  
[www.intercontec.biz](http://www.intercontec.biz)





**intercontec**  
products

# 923 Clamping Ring with bend protection

**TE part number: A2-0164-001-000**  
**IC reference number: A2.164.01**

## Material

clamp ring  
bend protection

brass, nickel plated  
PU UL 94/ V0


## Technical Data

clamping range

to  $\varnothing 11$  mm

## for:

923 plug and 923 extensions,  
with connection thread M24x1.



## Main Dimensions

clamp ring  
with bend protection

Y6-H208-000-0EN issued: 20.08.2018/MHu

© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH  
Bernrieder Straße 15  
94559 Niederwinkling, Germany  
+49 9962 2002 - 0  
[intercontec@te.com](mailto:intercontec@te.com)  
[www.intercontec.biz](http://www.intercontec.biz)

