



Discover more details and matching accessories online!

Versatile sound level meter

Features

- Sound level meter with basic functions for measuring noise in areas such as, environment, mechanical applications, car industry and much more
- Measures the sound intensity in the workplace
- Helps in differentiating between normal noise influences, and excessive noise, nuisances e.g. in a production hall
- 1 Data interface RS-232, included
- Multi measuring functions:
 - Lp: Standard sound level measuring function
 - Leq: Energy equivalent sound level measuring mode (type A)
 - Ln: Shows the deviation from a pre-defined limit in %

- Selectable methods of evaluation:
 - A: As sensitive as the human ear
 - C: Sensitive for noisier environmental conditions, where there are machines, plant, motors etc.
 - F: For areas with constant sound intensity
- Limit value function: programmable value for the maximum level value
- Track function for continuous recording of changing environmental conditions
- Peak Hold function to capture peak value
- Internal memory for 30 measured values, transferable to PC with SAUTER ATC-01
- 2 Delivered in a robust carrying case

Technical data

- Measuring precision: 3 % of [Max]
- Battery operation, batteries standard (4×1.5 V AAA)
- Overall dimensions W×D×H 223×62×25 mm
- Net weight approx. 0,20 kg

STANDARD

OPTION

Model	Type	Measuring range	Readout	Option
				Factory calibration certificate
SAUTER	Lp A	[Min]-[Max] dB	[d] dB	KERN
	Leq C			
	Ln F			
SU 130		30 – 130	0,1	961-281