

Windy 130 IF



NEW



Standardausrüstung:

• 5.209.0077
Schlauch 2,5 m



• 6.205.0109



• 3.754.0005



• 3.754.0015



• 3.754.0004



• 3.754.0168



300 mm

• 3.754.0169



• 3.754.0170



• 5.212.0040



• 3.752.0032



• 3.752.0114



• Netzkabel 7,5 m

Sonderzubehör

- Art.-Nr.: 5.212.0022 Papiersammelfilter-Satz
- Art.-Nr.: 5.212.0043 Stofffilter
- Art.-Nr.: 5.212.0006 Kassettenfilter
- Art.-Nr.: 5.212.0010 HEPA-Filter
- Art.-Nr.: 3.754.0205 Boden/Teppichbürste mit Rädern
- Art.-Nr.: 3.754.0081 Teppichbürste Turbo

Ausgestattet mit:

- Hochleistungs-By-Pass-Motor.
- Ansaugsystem mit By-Pass-Kühlung.
- Edelstahltank.
- Stoßsicherem Transportwagen.
- Schwimmerventil.
- Waschbarem Filter.
- 7,5 m Netzkabel.
- Zubehörsatz Ø 35.
- Handlichem Zubehöralter.

Windy 130 IF

Art.-Nr.:	8.250.0001
Spannung	220-240V ~ 50-60Hz
Motorart - Leistung (max.)	1 - 1200 (1400) W
Säulenunterdruck	24 kPa/2400 mmH ₂ O
Luftansaugung	65 l/s
Gesamtvolumen/Staub/Flüssigkeit	30 l./15 l./17 l.
Abmessung/Gewicht	37x37x71 cm / 8,5 Kg