



Elektrische Werte

*Bemessungsstrom max. 30 A
Durchgangswiderstand < 3 mOhm

Werkstoff


Kontakt Messing, vergoldet

Anschluß

Anschlußart crimp
Anschlußbereich 0,35- 2,5 mm²
für Isolationscrimp max. Isolations ø2,3 mm
Abisolierlänge 7 mm
Crimpeinstellungen sind individuell zu wählen

Mechanische Werte

Steckzyklen 500



Hauptabmessungen
Kontaktstift

Werkzeuge (nicht im Lieferumfang enthalten)

digitale Crimpzange	Best.-Nr.: C0.236.00
(analoge Crimpzange	Best.-Nr.: C0.201.00)
(Positioniereinsatz für 2 mm Kontakte	Best.-Nr.: C0.004.00)
Ausbauwerkzeug und Hülse für 2 mm Kontakte	Best.-Nr.: C4.005.00+C4.007.00



Electrical data

*rated current	max 30A
contact resistance	<3 mOhm

Material


contact	brass, gold plated
---------	--------------------

Termination

kind of termination	crimp
cross section	0.35 - 2.5mm ²
stripping length	7mm
crimp settings	select individually

Mechanical data

mating cycles	500
---------------	-----



Main Dimensions

contact pin

Tools (not part of product contents)

digital crimping tool	order code: C0.236.00
(analog crimping tool	order code: C0.201.00)
(positioning insert for 2mm contact	order code: C0.004.00)
removing tool and sleeve for 2mm contact	order code: C4.005.00+C4.007.00