

**Artikel Nr.: 862168**

Netzgerät, BASIC, CV, Q8H-24-150W



IP20 CE

**Elektrische Daten**

Betriebsart	spannungskonstant	Eingangsspannung	220-240V AC/50-60Hz
Leistung	150,00 W	Leistungsfaktor	0,95
Ausgangsspannung	24V DC	Anschlußmöglichkeit	Klemme
Ausgangsstrom	0-6250 mA		


**Produkteigenschaften**

Schutzklasse II	Überspannungsschutz
SELV Schutzkleinspannung	Lampenbetriebsgerät 110
Kurzschlußfest	Möbeleinbau geeignet
Überlastschutz	ErP Standby-Stromverbrauch < 0,5 W
Übertemperaturschutz	LVD Sicherheit nach EN 61347
Sicherheitstrafo	EMC Funkentstörung + Störfestigkeit nach EN 55015 + EN 61547
nicht dimmbar	EMC Netzstromoberwellen + Flicker nach EN 61000-3-2 + EN 61000-3-3

Schwarze Felder sind zutreffend / graue Felder sind nicht zutreffend

**Artikel Nr.: 862168**

Netzgerät, BASIC, CV, Q8H-24-150W

**Abmessungen und Gewicht****Grenzwerte**

Länge	210,00 mm	Betriebstemperatur	-20°C - +50°C
Breite	67,00 mm	Gehäusetemperatur	85 °C
Höhe	34,00 mm	max. Menge Sicherungsautomaten	B10A=2, B16A=4, C10A=6, C16A=9
Durchmesser	0,00 mm	max. Einschaltstrom	60A/300µs
Gewicht	556 g	kapazitive Last	591,2nF

Article No.: 862168

Power supply unit, BASIC, CV, Q8H-24-150W












IP20 CE

**Electrical Characteristics**

Operating mode	constant voltage	Input voltage	220-240V AC/50-60Hz
Power	150,00 W	Power factor	0,95
Output voltage	24V DC	Connection possibility	clamp
Output current	0-6250 mA		


**Product features**

	Protection class II		Overvoltage protection
SELV	Low voltage protection		Lamp control gear 110
	Short circuit protection		Suitable for furniture installation
	Overload protection	ErP	Standby-power consumption < 0,5 W
	Overheating protection	LVD	Safety according to EN 61347
	Safety transformer	EMC	Interference suppression + immunity according to EN 55015 + EN 61547
	not dimmable	EMC	Mains harmonics + flicker according to EN 61000-3-2 + EN 61000-3-3

Black fields are applicable / gray fields are not applicable

**Article No.: 862168**

Power supply unit, BASIC, CV, Q8H-24-150W

**Dimensions & Weight****Absolute maximum ratings**

Length	210,00 mm	Operating temperature	-20°C - +50°C
Width	67,00 mm	Case temperature	85 °C
Height	34,00 mm	max. amount of circuit breakers	B10A=2, B16A=4, C10A=6, C16A=9
Diameter	0,00 mm	max. inrush current	60A/300µs
Product weight	556 g	capacitive load	591,2nF