


Artikel Nr.: 862220

Netzgerät, BASIC, DIM, CV 12V 12-50W












IP20 CE

### Elektrische Daten

Betriebsart	spannungskonstant	Eingangsspannung	220-240V AC/50-60Hz
Leistung	12,00-50,00 W	Leistungsfaktor	0,95
Ausgangsspannung	12V DC	Anschlußmöglichkeit	Klemme
Ausgangsstrom	1000-4610 mA		


### Produkteigenschaften

	Schutzklasse II		Überspannungsschutz
SELV	Schutzkleinspannung		Lampenbetriebsgerät 110
	Kurzschlußfest		Möbeleinbau geeignet
	Überlastschutz	ErP	Standby-Stromverbrauch < 0,5 W
	Übertemperaturschutz	LVD	Sicherheit nach EN 61347
	Sicherheitstrafo	EMC	Funkentstörung + Störfestigkeit nach EN 55015 + EN 61547
	dimmbar - Phasen-/abschnitt	EMC	Netzstromoberwellen + Flicker nach EN 61000-3-2 + EN 61000-3-3

Schwarze Felder sind zutreffend / graue Felder sind nicht zutreffend

**Artikel Nr.: 862220**

Netzgerät, BASIC, DIM, CV 12V 12-50W




**Abmessungen und Gewicht**

**Grenzwerte**

Länge	184,00 mm	Betriebstemperatur	-20°C - +50°C
Breite	61,00 mm	Gehäusetemperatur	70 °C
Höhe	33,00 mm	max. Menge Sicherungsautomaten	B10A=32, B16A=51, C10A=32, C16A=51
Durchmesser	0,00 mm	max. Einschaltstrom	20A/100µs
Gewicht	g	kapazitive Last	19244uF

Article No.: 862220

Power supply unit, BASIC, DIM, CV 12V 12-50W












IP20 CE

### Electrical Characteristics

Operating mode	constant voltage	Input voltage	220-240V AC/50-60Hz
Power	12,00-50,00 W	Power factor	0,95
Output voltage	12V DC	Connection possibility	clamp
Output current	1000-4610 mA		


### Product features

	Protection class II		Overvoltage protection
SELV	Low voltage protection		Lamp control gear 110
	Short circuit protection		Suitable for furniture installation
	Overload protection	ErP	Standby-power consumption < 0,5 W
	Overheating protection	LVD	Safety according to EN 61347
	Safety transformer	EMC	Interference suppression + immunity according to EN 55015 + EN 61547
	dimnable - leading/trailing edge	EMC	Mains harmonics + flicker according to EN 61000-3-2 + EN 61000-3-3

Black fields are applicable / gray fields are not applicable

**Article No.: 862220**

Power supply unit, BASIC, DIM, CV 12V 12-50W

**Dimensions & Weight****Absolute maximum ratings**

Length	184,00 mm	Operating temperature	-20°C - +50°C
Width	61,00 mm	Case temperature	70 °C
Height	33,00 mm	max. amount of circuit breakers	B10A=32, B16A=51, C10A=32, C16A=51
Diameter	0,00 mm	max. inrush current	20A/100µs
Product weight	g	capacitive load	19244µF