

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** OPPLE Lighting

**Supplier's address:** Carlo Schmitz, Head of Marketing Europe, Meerenakkerweg 1-07, 5652AR, Eindhoven, Netherlands

**Model identifier:** 543022023500

## Type of light source:

|                                                     |                        |                                 |      |
|-----------------------------------------------------|------------------------|---------------------------------|------|
| Lighting technology used:                           | LED                    | Non-directional or directional: | NDLS |
| Light source cap-type (or other electric interface) | 220-240 V AC; 50/60 Hz |                                 |      |
| Mains or non-mains:                                 | MLS                    | Connected light source (CLS):   | Nein |
| Colour-tuneable light source:                       | Nein                   | Envelope:                       | -    |
| High luminance light source:                        | Nein                   |                                 |      |
| Anti-glare shield:                                  | Nein                   | Dimmable:                       | No   |

## Product parameters

| Parameter | Value | Parameter | Value |
|-----------|-------|-----------|-------|
|-----------|-------|-----------|-------|

### General product parameters:

|                                                                                                                                                       |                        |                                                                                                                                                            |                        |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer                                                                         | 38                     | Energy efficiency class                                                                                                                                    | D                      |
| Useful luminous flux ( $\phi_{\text{use}}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 5 320 in Sphere (360°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 4 000                  |
| On-mode power ( $P_{\text{on}}$ ), expressed in W                                                                                                     | 38,0                   | Standby power ( $P_{\text{sb}}$ ), expressed in W and rounded to the second decimal                                                                        | 0,00                   |
| Networked standby power ( $P_{\text{net}}$ ) for CLS, expressed in W and rounded to the second decimal                                                | -                      | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set                                                         | 80...89                |
| Outer dimensions                                                                                                                                      | Height                 | Spectral power distribution in the                                                                                                                         | See image in last page |
|                                                                                                                                                       | Width                  |                                                                                                                                                            |                        |

|                                                                                                                         |       |       |                                       |                |
|-------------------------------------------------------------------------------------------------------------------------|-------|-------|---------------------------------------|----------------|
| without separate control gear, lighting control parts and non-lighting control parts, if any (millimetre)               | Depth | 1 310 | range 250 nm to 800 nm, at full-load  |                |
| Claim of equivalent power <sup>(a)</sup>                                                                                |       | -     | If yes, equivalent power (W)          | -              |
|                                                                                                                         |       |       | Chromaticity coordinates (x and y)    | 0,380<br>0,380 |
| <b>Parameters for LED and OLED light sources:</b>                                                                       |       |       |                                       |                |
| R9 colour rendering index value                                                                                         |       | 7     | Survival factor                       | 0,90           |
| the lumen maintenance factor                                                                                            |       | 0,96  |                                       |                |
| <b>Parameters for LED and OLED mains light sources:</b>                                                                 |       |       |                                       |                |
| displacement factor (cos $\phi_1$ )                                                                                     |       | 0,90  | Colour consistency in McAdam ellipses | 4              |
| Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage. |       | -(b)  | If yes then replacement claim (W)     | -              |
| Flicker metric (Pst LM)                                                                                                 |       | 1,0   | Stroboscopic effect metric (SVM)      | 0,4            |

(a) '-': not applicable;

(b) '-': not applicable;

