







W913808740121



⚡ ⚠ DANGER / 危險

HAZARD OF ELECTRIC SHOCK, EXPLOSION, OR ARC FLASH


Disconnect all power before servicing equipment.

Failure to follow these instructions will result in death or serious injury.






可能有触电、爆炸或者电弧灼伤的危险

在此电力设备上进行操作时，请先断开所有电源。

不遵循上述规定将可能导致人员伤亡。



$\sim$ = Alternative current coil
 $\dots$ = Continuous current coil
 LC = Continuous 100mA current coil
 AC/DC = Alternative and continuous current coil



					AWG	
		[mm ²]	[mm ²]			
	LC2DT203	10 mm 3/8"	1...2,5	1...2,5	AWG 14-18 CU 75°C Solid or Stranded	3.5 mm
	LC2DT253	10 mm 3/8"	1...4	1...4	AWG 10-18 CU 75°C Solid or Stranded	4 mm
	LC2DT323	13 mm 1/2"	1...10	-	AWG 10-14 CU 75°C Solid	4 mm
	LC2DT403	13 mm 1/2"	1...10	-	AWG 8-14 CU 75°C Stranded	4 mm
	LC2DT...3	8 mm 5/16"	1...2,5	1...2,5	AWG 14-18 CU 75°C Solid or Stranded	3.5 mm