



Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **Between Series Adapter**

Body Orientation: **Straight**

Side A Interface: **N Type**

Side A Gender: **Plug**

Side B Interface: **4.3/10**

Features

Product Type Features

Connector Interface Adapter Type	Between Series Adapter
Side A Interface	N Type
Side A Gender	Plug
Side B Interface	4.3/10
Side B Gender	Plug
Sealable	No

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Housing Features

Body Orientation	Straight
------------------	----------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application



Operating Frequency	10 GHz
---------------------	--------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 2081554-1 ADAPTER 4.3-10 FEMALE TO 4.3-10 FEMALE	 TE Part # 2016294-1 C/A,ST PLUG TO ST PLUG,SCREW, 1M 1/2" SF	 TE Part # 1-2016294-6 C/A,ST PLUG TO ST PLUG,SW, 0.3M 1/2" S
---	---	---

Customers Also Bought





TE Part #1879451-6
TE 600W 2R7 5% Bracket




TE Part #1059724-1
4583 2240 02



TE Part #8-53555-1
SOLIS SPD 22-16COMM 22-18MIL 2



TE Part #1-1625995-2
HSC75 50K 10%



TE Part #1059733-1
BSA, OSP Jack-SMA Jack BHD 4584 2244 02



TE Part #2-1609113-7
1CUFS1=F8298



TE Part #1-2273045-4
M12 x 1.0 straight socket pigt shld A



TE Part #YDTS26G17-35PNV001
PLUG ASSY



TE Part #YDTS26G15-18SNV001
PLUG ASSY



TE Part #YDTS20F25-37PC0000
RECP ASSY

Documents

Product Drawings
ADAPTER N MALE TO 4.3-10 MALE

English

CAD Files
3D PDF
3D

Customer View Model
ENG_CVM_CVM_2081558-1_A.2d_dxf.zip
English

Customer View Model
ENG_CVM_CVM_2081558-1_A.3d_igs.zip
English

Customer View Model
ENG_CVM_CVM_2081558-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Product Specification

English