



Connectors > RF Connectors > Coax Connectors > F Type Connector: Jack, Right-Angle, Elbow Jack PCB, 75 Ohm



RF Interface: **F Type**

RF Connector Style: **Plug**

RF Connector Mated Outer Diameter (Approximate): **9.5 mm [.374 in]**

Impedance: **75 Ω**

Compatible With RF Cable Type: **CT100**

All F Type Connector: Jack, Right-Angle, Elbow Jack PCB, 75 Ohm (0)

Features

Product Type Features

RF Interface	F Type
RF Connector Style	Plug
Compatible With RF Cable Type	CT100
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	75 Ω
-----------	------

Body Features

Cable Connector Orientation	Straight
-----------------------------	----------



Body Material	Brass
Body Plating Material	Nickel

Termination Features

Termination Method to Wire & Cable	Twist-On
------------------------------------	----------

Mechanical Attachment

RF Connector Coupling Mechanism	Screw
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

RF Connector Mated Outer Diameter (Approximate)	9.5 mm[.374 in]
---	-----------------

Operation/Application

Operating Frequency	1 GHz
---------------------	-------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #5-826936-0
AMP AMPMODU II PIN HDR.



TE Part #1-1705951-1
Modular Jack SE, 8/8, Gold flash



TE Part #2-1623925-2
CFR100 5% 220R



TE Part #216000-2
6P. TOOLLESS MOD J.



TE Part #2-1676123-2
1/2W SM M/OX 5% 6R2



TE Part #6-1676914-6
YR1 0.1% 590R



TE Part #CAT-HST-RT375
RT-375 Heat Shrink Tubing



TE Part #1623730-4
BCHE 4 W 15R 5%



TE Part #696202-1
HAND TOOL, SERVICE

Documents

- CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-1814822-5_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1814822-5_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1814822-5_C.3d_stp.zip](#)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Economy RF Coaxial Connectors

English

Product Specification

English

Agency Approvals

UL Report

English