




Switches > DIP & SIP Switches



DIP & SIP Switch Type: **DIP**
Switch Contact Plating Material: **Gold**
Case Color: **Blue**
Case Material: **Polyester GF**
Sealed Device: **Yes**

Features

Product Type Features

DIP & SIP Switch Type	DIP
Sealed Device	Yes
Actuator Style	Rocker (Top Actuated)

Configuration Features

Number of Positions	4
Number of Switches	4
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Contact Current Rating	1 A
Operating Voltage	40 VDC

Body Features

Sealing Method	Strippable Transparent Protective Seal
Product Orientation	Vertical
Case Color	Blue
Case Material	Polyester GF



Contact Features

	30 µin
PCB Contact Termination Area Plating Material	Tin
Switch Contact Plating Material	Gold
Contact Base Material	Copper Alloy

Termination Features

Termination Post & Tail Length	3.56 mm[.14 in]
Termination Method to PCB	Through Hole - Solder

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Product Length	12.19 mm[.48 in]
Product Height	8.64 mm[.34 in]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
Packaging Quantity	25

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 435668-7 LO PROFILE DIP SW 8P AU	 TE Part # 3-5435668-4 DIP SW 4 POSN W/TAPE AU	 TE Part # 2-5435668-8 DIP SW 8 POSN W/TAPE AU	 TE Part # 2-5435668-5 DIP SW 6 POSN W/TAPE AU
--	--	---	---

Customers Also Bought

 TE Part #5-535541-1 03 MODIV VRT SR CE 100/115	 TE Part #8-1437653-0 6PCV-16-006=6PCV ASSEMBLY	 TE Part #2199230-3 M.2 0.5PITCH 4.2H KEY B 15U" AU	 TE Part #2-1761603-5 IDC LOW PRO HDR 14P VERT BLUE
 TE Part #3-1623788-1 SQM5 R05 5% (WIRE)	 TE Part #DTM13-12PA-R008 HDR, 12P, BLK, RA EEC, NI/CU, A	 TE Part #1-1393766-8 R10-E1X4-115V=R10	 TE Part #5520257-2 MJ,TE,4P,PNL STOPS





TE Part #4-1393144-6
[K10P-11A55-120=K10/K20](#)

TE Part #2267124-1
[CMC RECEPT ASSY,SIZE 28, POSTED](#)

Documents

Product Drawings

[DIP SW 4 POSN SEALED](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_3-5435640-5_A1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_3-5435640-5_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_3-5435640-5_A1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-5435640-5_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-5435640-5_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-5435640-5_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

