

Adapter N-Stecker auf SMA Stecker 1m Kabel

N o m . A t t e n u a t i o n (d b / 1 0 0 m)

1 0 M H z	9 , 0 0
4 0 M H z	1 8 , 0 0
8 0 M H z	2 6 , 0 0
1 0 0 0 M	2 9 , 5 0
1 5 0 0 M	3 6 , 5 0
1 7 5 0 M	3 9 , 5 0
2 1 5 0 M	4 4 , 0 0
2 4 0 0 M	4 7 , 0 0
3 0 0 0 M	5 4 , 0 0
3 7 0 0 M	6 0 , 0 0
4 3 0 0 M	6 8 , 0 0
4 9 0 0 M	7 6 , 0 0
5 8 0 0 M	8 8 , 0 0

RoHS
Konform



A t t e n u a t i o n o n l e n g t h 1 0 m
O n 8 0 0 M H z @ 1 0 m = 2 , 6 d b
O n 1 7 5 0 M H z @ 1 0 m = 3 , 9 d b

ATT @ Freq.	800 MHz	1800 MHz	2500 MHz	3500 MHz
1 m coax length	0,3 dB	0,4 dB	0,5 dB	0,6 dB
5 m coax length	1,3 dB	2,0 dB	2,4 dB	2,9 dB
10 m coax length	2,6 dB	4,0 dB	4,8 dB	5,8 dB
15 m coax length	3,9dB	6,0 dB	7,2 dB	8,7 dB
20 m coax length	5,2dB	8,0 dB	9,6 dB	11,8 dB
100 m coax length	26 dB	40 dB	48 dB	58 dB



4 021064 034950



Art.Nr.103495