



Connectors > RF Connectors > Coax Connectors



RF Interface: **Mini BNC**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **7.49 mm [.295 in]**

Impedance: **75 Ω**

Compatible With RF Cable Type: **RG 179**

Features

Product Type Features

RF Interface	Mini BNC
RF Connector Style	Jack
Compatible With RF Cable Type	RG 179
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	75 Ω
-----------	------

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Plating Material	Nickel



Contact Features

Crimp Type	Hexagonal Crimping
RF Connector Center Contact Underplating Material	Copper, Nickel
RF Connector Center Contact Plating Material	Gold (Au)
RF Connector Center Contact Material	Phosphor Bronze

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Attachment Style	Rear Mount
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	With

Dimensions

RF Connector Mated Outer Diameter (Approximate)	7.49 mm[.295 in]
---	------------------

Operation/Application

Operating Frequency	2 GHz
---------------------	-------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Additional Features	Hardware Included
Grade	Commercial
Dielectric Material	PTFE

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219)



SVHC > Threshold:
Pb (4% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.


Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #634051-000
202K121-25/225-0



TE Part #5205817-1
KIT SCREWLOCK FEMALE



TE Part #5-1478762-1
Metal backshell 9 way Top Entry-KIT



TE Part #YDTS32F13NV0010000
DUST COVER ASSEM



TE Part #901727-000
S02-18-R



TE Part #657863-000
S1125-KIT-8



TE Part #ZPF000000000099685
DMC-M 99-01 SN



TE Part #1-1478903-0
SMA STR PLG DS RG402 GSS



Documents

Product Drawings
[PLUG KIT, STRAIGHT, MINI BNC](#)
English

CAD Files
[3D PDF](#)
3D
Customer View Model
[ENG_CVM_CVM_1274568-3_D.2d_dxf.zip](#)
English
Customer View Model
[ENG_CVM_CVM_1274568-3_D.3d_igs.zip](#)
English
Customer View Model
[ENG_CVM_CVM_1274568-3_D.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
[Mini BNC Connectors](#)
English

Product Specifications
[Product Specification](#)
English
[Product Specification](#)
English

Instruction Sheets
[Instruction Sheet \(U.S.\)](#)
English