BUSINESS & PRODUCTIVITY PCS

Cubi NUC AI+ 3MG

CUBI NUC AI+ 3MG-006DE

Be Your Window To The World


Der MSI Cubi NUC AI+ 3MG ist ein Copilot+ PC, der integrierte KI für eine intelligentere Produktivität, ein optimiertes Multitasking und eine gesteigerte Geräteleistung bietet. Die KI wird von einem Intel Core Ultra Prozessor mit NPU angetrieben und ist für den Einsatz in den Bereichen Bildung, Wirtschaft und soziale kreative Arbeit konzipiert. Der Fingerabdrucksensor am Power-Knopf bietet zusätzliche Sicherheit für ihre Daten. Entdecken Sie die Zukunft!



Picture and logos

SELLING POINTS

- Windows 11 Home - MSI empfiehlt Windows 11 Pro für Unternehmen
- 0.51 Liter Volumen (37.5mm Höhe) mit VESA-montierbarem Design
- Bis zu Intel® Core™ Ultra 9 Prozessor 386H mit Intel® AI Boost NPU
- Dual Channel DDR5 SO-DIMMs Arbeitsspeicher
- Zwei Thunderbolt™ 4 Anschlüsse für eine Unterstützung von Setups mit bis zu 4 Displays
- Dual 2.5G LAN, werkzeugfreies Design für einfache Wartung und mit Kabelorganisierer
- Power Button mit Fingerabdruck für erhöhte Sicherheit
- MSI Power Link: Der Cubi NUC kann über die MSI Power Link-Technik über einen Monitor mit Strom versorgt werden
- Der Power Meter ermöglicht Energiesparen mit einem Klick, die Berechnung der CO2-Emissionen und die Schätzung der Stromkosten
- Hergestellt aus PCR-recyceltem Kunststoff; FSC™-zertifizierter Karton; Abfallreduzierung durch recycelte Formmasse (100 % recycelbar); In der Fabrik zu 99 % mit erneuerbarer Energie hergestellt



1. 1x USB 2.0 Typ A
2. 1x USB 10Gbps Typ A
3. 1x USB 10Gbps Typ C
4. 1x Power Button mit Fingerabdrucksensor
5. 1x Stromanschluss
6. 1x HDMI Ausgang(unterstützt 4K @60Hz nach HDMI 2.1/ unterstützt MSI Power Link)
7. 2x RJ45 (2.5G)
8. 1x HDMI Ausgang(unterstützt 4K @60Hz nach HDMI 2.1)
9. 1x Kensington Lock
10. 1x Externer Power Knopf Pin Anschlusss
11. 1x Thunderbolt 4 (DP 1.4 alt-mode bis zu 4K@60Hz / PD-out 15W / unterstützt PD-in bis zu 98W)
12. 1x Thunderbolt 4 (DP 1.4 alt-mode bis zu 4K@60Hz / PD-out 15W)

"2026-05-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

Cubi NUC AI+ 3MG

CUBI NUC AI+ 3MG-006DE

SPECIFICATION

Betriebssystem	Betriebssystem	Windows 11 Pro
	Operating Systems	Windows 11 Pro
Prozessor	CPU Number	Intel Core Ultra 9 processor 386H
	CPU Clock	2.1GHz
	CPU Cores	16
	TDP	25W
	Cache	18 MB Intel® Smart Cache
	Threads	16
	Max Turbo Frequency	up to 4.90 GHz
	CPU Cooler	Air cooling
	Platform TOPS	Up to 100 TOPS
	NPU TOPS	Up to 50 TOPS
Model	MKT Name	Cubi NUC AI+ 3MG
	MKT Spec	Cubi NUC AI+ 3MG-006DE
	Color	ID1/Black-Black-Black
	SKU Number	00B21111-006
	Part No	9S6-B21111-006
	Model	B211
Chipsatz	Chipsets	Soc
Arbeitsspeicher	Memory Size	32GB(16GB*2)
	Memory Type	DDR5 SDRAM
	Memory Speed	2800(5600)MHz
	Module Type	SO-DIMM
	Memory Slot(Total)	2
	Memory Slot(Free)	0
	Max Capacity	Max 32GB
	Memory Slot (Total/Free)	2/0
Grafik	GPU1 VRAM Size	N/A
	VGA I/O Port	N/A
	GPU1 Vendor	N/A
	GPU1 MKT Name	N/A
	GPU1 Number	N/A
Speicher	SSD Interface	PCIe GEN4x4 NVMe
	SSD Form Factor	M.2 2280 M-KEY
	SSD Config	1TB*1
	SSD Size	1TB
	HDD1 Interface	N/A
	HDD1 Form Factor	N/A
	HDD1 Size	N/A
	HDD1 RPM	N/A
	ODD(Type)	N/A
	ODD Height	N/A
	ODD Type	N/A
	M.2 slots (Total/Free)	1/0
	2.5" Drive Bays (Total/Free)	0/
	3.5" Drive Bays (Total/Free)	0/
	M.2 slots(Total)	1
	M.2 slots(Free)	0
	2.5" Drive Bays (Free)	0
	3.5" Drive Bays(Free)	0
Kommunikation	LAN	N/A
	WLAN Version	Wi-Fi 7+BT
	BT Version	5.4
	WLAN	FOXCONN/MT7925B22M
Schnittstellen (Vorne)	USB 2.0 Type A	1
	Audio Headphone-out (HiFi/SPDIF)	N/A
	USB 3.2 Gen 2 (10G) Type C	1
	USB 3.2 Gen 2 (10G) Type A	1
	Copilot Button	1

"2026-05-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

Cubi NUC AI+ 3MG

CUBI NUC AI+ 3MG-006DE

Schnittstellen (Seite)	USB 2.0 Type A	1
	USB 3.2 Gen 2 (10G) Type C	1
	USB 3.2 Gen 2 (10G) Type A	1
Schnittstellen (Rückseite)	Thunderbolt (R)	2x (Thunderbolt 4)
	RJ45	2
	HDMI out	2x (HDMI v2.1 Support up to 4K@60Hz)
	Lock type	Kensington Lock
Power	Power	120W
	Power Certification	N/A
	Formfactor	N/A
	Type	ADAPTOR
VESA	VESA size	100 x 100 mm
Garantie	Warranty	36months
Abmessungen & Gewicht	Product Dimension (WxDxH) (mm)	119.6 x 115.2 x 37.5
	Product Dimension (WxDxH) (inch)	4.71 x 4.54 x 1.48
	Inside Carton Dimension (WxDxH) (mm)	205 x 220 x 94
	Inside Carton Dimension (WxDxH) (inch)	8.07 x 8.66 x 3.7
	Outer Carton Dimension Standard (WxDxH) (mm)	221 x 506 x 469
	Outer Carton Dimension Standard (WxDxH) (inch)	8.7 x 19.92 x 18.46
	Weight (Net kg)	0.50
	Net Weight (lbs)	1.1
	Weight (Gross kg)	1.45
	Gross Weight (lbs)	3.2
	Liter	0.7L
	Pint	0.7L
Lagerung & Zertifikationen	Regulatory Compliance	BSMI, CB/CE, CEC, ERP lot 3, Energy Star, Epeat Sliver, FCC(Class B), RCM(C-Tick), RH, UL(CUL), VCCI
	Operating, Storage Temperature	0° C ~ 35° C ; -20° C ~ 60° C
	Operating, Storage Humidity	0% ~ 85%;0% ~ 90%
Zubehör	AC Adaptor	1
	Power Cord	1
	Warranty Card	N/A
	Quick Guide	3
	User Manual	N/A
	VESA Mount kit	1
	Keyboard	N/A
	Keyboard Interface	N/A
	Mouse	N/A
	Mouse Interface	N/A
	Power Switch	N/A
Barcode Info	EAN	4711377436441
Security	TPM module	dTPM
	Chassis Lock	Kensington Lock

“2026-05-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products.”