



Connectors > RF Connectors > Coax Connectors



RF Interface: **BNC**

RF Connector Style: **Plug**

RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**

Impedance: **50 Ω**

Compatible With RF Cable Type: **Belden 8212**

Features

Product Type Features

Connector Seal & Plug Type	Gasket
RF Interface	BNC
RF Connector Style	Plug
Compatible With RF Cable Type	Belden 8212
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Plating Material	Nickel



Contact Features	
Crimp Type	Dual Crimp
RF Connector Center Contact Underplating Material	Nickel
	889 µin
RF Connector Center Contact Plating Material	Gold (Au)
RF Connector Center Contact Material	Brass
Termination Features	
Termination Method to Wire & Cable	Crimp
Mechanical Attachment	
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Cable Mount (Free-Hanging)
RF Contact Captivation Method	Mechanical
Detent	With
Dimensions	
RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]
Usage Conditions	
Insulation Option	Uninsulated
Operation/Application	
Operating Frequency	4 GHz
Packaging Features	
Packaging Method	Carton
Other	
Coupling Nut Base Material	Brass
Grade	Military
Dielectric Material	PTFE
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024
(241)

Candidate List Declared Against: JUL 2021
(219)

SVHC > Threshold:
Pb (3.7% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

 TE Part #5745174-1 CABLE CLAMP KIT,SZ 4	 TE Part #3-640441-6 06P MTA100 CONN ASSY WHT	 TE Part #1757819-9 AMPLIMITE,ASY,PLUG,STD,109,ZN,4,CT	 TE Part #5745833-1 CABLE CLAMP KIT,SZ 3
 TE Part #643075-6 06P MTA100 MOLDED COVER	 TE Part #1757823-7 AMPLIMITE,ASY,PLUG,STD,90,ZN,1,CT	 TE Part #1393249-5 W58-XB1A4A-1=W58	 TE Part #1757820-8 AMPLIMITE,ASY,RCPT,STD,109,ZN,3,CT



TE Part #1-1609112-2
[15CE1=F8272](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-5225395-0_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-5225395-0_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-5225395-0_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BNC Connectors

English

Product Specifications

Product Specification

English

Agency Approvals

UL Report

English