

Philips Series 6100 HX7400/01 Wiederaufladbare Zahnbürste

Marke : Philips

Artikel-Code: HX7400/01

Produktname : Series 6100 HX7400/01 Wiederaufladbare Zahnbürste

- Erinnerungsfunktion
 - SmartTimer und BrushPacer
 - Putzmodi und Intensitätsstufen
 - 21 Tage Akkulaufzeit
 - Visueller Drucksensor
 - Next-Generation Sonicare Technologie
 - Zusätzliche Pflege für empfindliche Zähne
- Philips Sonicare Series 6100 Wiederaufladbare Zahnbürste

Philips Series 6100 HX7400/01 Wiederaufladbare Zahnbürste:

Fortgeschrittliche Pflege für empfindliche(s) Zähne/Zahnfleisch

Entfernt bis zu 10 x mehr Plaque als eine Handzahnbürste

Die Philips Sonicare 6100 verfügt über eine Sonicare Technologie der nächsten Generation, einen speziellen Modus für empfindliche Zähne und empfindliches Zahnfleisch, einen S2 Sensitive Bürstenkopf und drei Intensitätsstufen. Außerdem wissen Sie dank visueller Andruckkontrolle, wenn Sie zu viel Druck verwenden.



Merkmale		Sonstige Funktionen	
Zweck *	Erwachsener	Garantiezeit	2 Jahr(e)
Zahnbürstentyp *	Schallzahnbürste	Lieferumfang	
Anpassbare Geschwindigkeit *	✓	Anzahl enthaltener Griffe *	1 Stück(e)
Anzahl Geschwindigkeiten	3	Anzahl enthaltener Bürstenköpfe *	1 Stück(e)
Integrierter Timer *	✓	Ladegerät	✓
Timer-Dauer-Modi	2 min, 4 x 30 sec	Bürstenköpfe enthalten	1 S2 Sensitive
Anzahl der Zahnbürsten-Modi *	2	USB-Ladegerät enthalten	✓
Zahnbürsten Modi *	Sensibel	Anzahl der Ladegeräte	1
Zahnbürstenfrequenz (Pulsierungen) *	62000 Bewegungen pro Minute	Akku/Batterie	
Drucksensor	✓	Akku-/Batterietechnologie	Lithium-Ion (Li-Ion)
Produktfarbe *	Weiß	Akku	✓
Anzeige zum Bürsten wechseln	✓	Batteriestandsanzeige	✓
Griff Eigenschaften	Ergonomisch	Technische Details	
Anzeigelicht	✓	Betriebsdauer (Voller bis leerer Akku)	21 days
Mobile App-Unterstützung *	✗	Smartimer	None
Energie		Reinigungsmodi	For exceptional everyday cleaning
Energiequelle *	Akku	Empfindlichkeits-Modi	For sensitive teeth and gums
Batteriebetrieben	✓	Timer	BrushPacer and Smartimer
Akku-/Batterietyp *	Integrierte Batterie	Einfach aufsteckbarer Bürstenkopf	✓
Akku-/Batteriebetriebsdauer	504 h	Druckrückmeldung	Light ring illuminates purple; Vibration and pulsing sound
Ladestation	✓		

Energie		Technische Details	
Wiederaufladbar	✓	Ersatz-Erinnerung	BrushSync lets you know when to replace your brush head
AC Eingangsspannung	100-240 V		



8720689021715

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity. Automated scraping, data mining, or harvesting for the purpose of training machine learning models, neural networks, or artificial intelligence systems is strictly prohibited without a commercial license.