



9-Port 2.5G GaN Power PoE++ Switch with 10G SFP+ Port (480W)


TPE-BG5091 (v1.xR)

- 8 x 2.5G PoE++ ports
- 1 x 10G SFP+ ports
- 480W PoE power budget
- High- efficiency GaN internal power supply
- Backward compatible with 10/100/1000Mbps devices
- Compatible with existing Cat5e or better cabling
- Rack mountable for installation flexibility
- 60Gbps switching capacity
- IEEE 802.3bz (2.5G) compliant
- Supports IEEE 802.3af/at/bt
- Lifetime Warranty
- NDAA / TAA compliant (U.S. and Canada only)

Expand your network's bandwidth and reduce traffic bottlenecks with TRENDnet's 9-Port 2.5G GaN Power PoE++ Switch with 10G SFP+ Port (480W), model TPE-BG5091. This 2.5G PoE++ switch is equipped with 2.5GBASE-T RJ-45 ports that provide multi-gigabit speeds capable of up to 2.5Gbps over your existing Cat5e or better cabling. The 10G SFP+ port provides a high-speed 10Gbps network uplinks or downlinks over long distances. This multi-gigabit PoE++ switch features a durable metal enclosure and can be rack mounted for setup flexibility.

TRENDnet's reliable 2.5G PoE++ switch is a cost-effective solution to increase your network's throughput. A 480W total PoE power budget on this multi-gig PoE++ GaN-powered network switch supplies up to 95W per PoE port. Easily network PoE devices, such as high-power wireless access points, IP cameras, digital signage, IPTV decoders, access controls, and more with this high-power 2.5 gigabit PoE++ switch.

This PoE++ switch uses GaN power technology. GaN technology allows power supply designs to be smaller and more efficient. Compared with traditional power supplies, a GaN power supply takes up to 40% less foot print, and the increased efficiency reduces heat generated by the internal power supply.



2.5G Ports

Equipped with 2.5GBASE-T RJ-45 ports that provide multi-gigabit speeds capable of up to 2.5Gbps over existing Cat5e or better cabling.



PoE++

A 480W total PoE power budget on this GaN power network switch supplies up to eight PoE++ devices with up to 95W per port.



10G SFP+

Offers one 10G SFP+ port for a high-speed network uplinks or downlink connections for long- distance networking.

FEATURES



Easy Installation

No configuration needed, simply connect network devices to the 2.5G multi-gig PoE++GaN - power network switch



2.5G Ports

Equipped with 2.5GBASE-T RJ-45 ports, this multi-gigabit PoE++ switch provides higher gigabit speeds capable of up to 2.5Gbps over existing Cat5e or better cabling



SFP+ Port

Equipped with a 10G SFP+ port for long distance fiber networking



PoE++

A 480W total PoE power budget on this 2.5GaN PoE++ switch supplies up to eight PoE/PoE+/PoE++ devices with up to 95W per port



GaN Power Supply

The GaN PoE switch features increased power efficiency while reducing heat and housing size



Backwards Compatibility

Backwards compatible with 10/100/ 1000Mbps legacy devices



Housing Design

Sturdy metal housing



Jumbo Frame

Sends larger packets, or Jumbo Frames (up to 12KB), for increased performance



Rack Mountable

1U rackmount design for installation flexibility



Switching Capacity



60Gbps switching capacity



LED Indicators

LED indicators on the GaN - powered network 2.5G PoE++ switch convey port status

NETWORKING SOLUTION



SPECIFICATIONS

Standards

- IEEE 802.1p
- IEEE 802.3
- IEEE 802.3u
- IEEE 802.3x
- IEEE 802.3ab
- IEEE 802.3ae
- IEEE 802.3af
- IEEE 802.3at
- IEEE 802.3bt
- IEEE 802.3bz

Device Interface

- 8 x 2.5GBASE-T PoE++ ports
- 1 x 10G SFP+ ports
- LED indicators

Data Transfer Rate

- Ethernet: 10Mbps (half duplex), 20Mbps (full duplex)
- Fast Ethernet: 100Mbps (half duplex), 200Mbps (full duplex)
- Gigabit: 2Gbps (full duplex)
- 2.5 Gigabit: 5Gbps (full duplex)
- Gigabit SFP: 2Gbps (full duplex)
- 10G SFP+: 20Gbps (full duplex)

Performance

- Data RAM Buffer: 1MB
- Switch Capacity: 60Gbps
- MAC Address Table: 4K entries
- Forwarding rate: 44.64Mpps (64-byte packet size)
- Jumbo Frame: 12KB

Power

- Input: 100 – 240V AC, 50/60Hz, internal power supply
- Max. consumption: 16.5W (no PD)

PoE

- PoE budget: 480W
- PoE++: Up to 95W per port
- Pins 1, 2, 7, 8 for power - and pins 3, 6, 4, 5 for power +
- Over current protection
- Short circuit protection

Fan/Acoustics

- 2 x Smart Fan

MTBF

- 204,000 hours

Operating Temperature

- 0° – 40° C (32° – 104° F)

Operating Humidity

- Max. 90% non-condensing

Dimensions

- 330 x 220 x 44mm (13 x 7.87 x 1.73 in.)

Weight

- 2.44g (5.29 lbs.)

Certifications

- CE
- FCC
- UL

Warranty

- Lifetime Warranty

Package Contents

- TPE-BG5091
- Rackmount kit
- Power cord (1.5m / 4.9 ft.)

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.

TRENDnet offers a lifetime warranty for all of its metal-enclosed network switches that have been purchased in the United States/Canada on or after 1/1/2015. Cooling fan and internal power supply carry a one-year warranty.