




Mechanical characteristics

interface dimensions acc. to

mating life

Components

center contact
outer contact
other metal parts
insulator

Electrical characteristics

impedance
frequency
return loss
working voltage
voltage proof
insulation resistance
contact resistance
center contact
outer contact

Environmental

operating temp.
RoHS compliant

Mechanische Eigenschaften

Steckgesicht nach

Steckzyklen

Bauteile

Innenkontakt
Außenkontakt
sonstige Metallteile
Isolierung

Elektrische Eigenschaften

Wellenwiderstand
Frequenz
Rückflussdämpfung
Betriebsspannung
Prüfspannung
Isolationswiderstand
Durchgangswiderstand
Innenkontakt
Außenkontakt

Umgebung

Betriebstemperatur
RoHS konform

BNC: IEC 61169-8

HD-BNC: without standard / ohne Norm
≥ 500

Materials / Material


copper alloy / Kupferleg.
brass / Messing
brass / Messing
PTFE


Finish / Oberfläche

Cu1Ni2Au0,3
Cu2Ni5
Cu2Ni5

75 Ω
0-4,5 GHz
up to / bis zu 4,5 GHz >typ. 25dB
≤ 170 V_{eff} / 50 Hz
500 V_{eff} / 50 Hz
≥ 10 GΩ
≤ 5.0 mΩ
≤ 2.5 mΩ

M 1:1



Änd./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name	Datum/ date	Name/ name	Gewicht/ weight (g)		
			gez./ drawn	01.04.2015	MA			
			gepr./ appr.	07.04.2015	KL	ca./approx.		
			Maßstab/ scale 5:1 (1:1)	Benennung/ title BNC Jack to Mini HD-BNC Plug BNC - Mini HD-BNC Adapter (f-m)				
			untel. Maße/ dim. without tolerances according to	Untert./ doc. type K	Zeichnungsnr./ drawing no. J01008A0092			
			Ersatz für/ replaces					
								 Maße/ dimensions: mm
								Original : DIN A4
								Blatt/ sheet 1 von/ of 1