
Kingbright

T-1 3/4 (5mm) BLINKING LED LAMP

P/N: L-56BID

HIGH EFFICIENCY RED



SPEC NO: DSAA4457 APPROVED: J. Lu REV NO: V.5 CHECKED: Allen Liu DATE: NOV/02/2005 DRAWN: F.LI

Kingbright

Selection Guid	e				
Part No.	Dice	Lens Type	lv (mcd) V=9V		Viewing Angle
			Min.	Тур.	2 θ 1/2
L-56BID	HIGH EFFICIENCY RED (GaAsP/GaP)	RED DIFFUSED	18	40	60 °

Note:

1. θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Min.	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red		627		nm	
λD	Dominant Wavelength	High Efficiency Red		625		nm	
Δλ1/2	Spectral Line Half-width	High Efficiency Red		45		nm	
lf	Forward Current	High Efficiency Red	8	22		mA	Min:VF=3.5V Typ:VF=5V
ISON	Supply Current	High Efficiency Red		8		mA	VF = 3.5V
Ison	Supply Current	High Efficiency Red		44		mA	VF = 14V
f	Blink Frequency	High Efficiency Red	1.5		3	Hz	VF = 3.5V~14V

Absolute Maximum Ratings at TA=25°C

Parameter	High Efficiency Red	Units			
Power dissipation	310	mW			
Forward Voltage	14	V			
Reverse Voltage	0.5	V			
Operating Temperature	-40°C To +70°C				
Storage Temperature	-40°C To +85°C				
Lead Solder Temperature [1]	260°C For 3 Seconds				
Lead Solder Temperature [2]	260°C For 5 Seconds				

Notes:

1. 2mm below package base.

2. 5mm below package base.

Kingbright

