


DIGITUS 25G DAC Cable SFP28 5m

DN-81245
EAN 4016032478836



DAC Cable SFP28 5 M DAC Cable 25 G 5m

DIGITUS® 25G SFP28 Passive Direct-Attach Copper Twinax Cable are a high-performance, energy-saving, short-range connectivity solution 25G Ethernet application, switches, high performance computer, data storage arrays and telecom system. It consists of a shielded twinax copper cable with pluggable connectors on either end. Passive DAC cable have no electrical components built into the cable assembly and recommend for short transmission distance. Typically 1~2m and max. 5m lengths.

It is suitable for short reach connection between two SFP28 ports in 25G interconnecting networking applications.

- Number of Lanes : Tx & Rx
- Connector Type: SFP28 to SFP28
- Channel Data Rate: 25.88243 Gbps

- Operating Temperature: 0 to +70°C
- Storage Temperature: -40 to +85°C
- Supply Voltage: 3.3V nominal
- Power consumption less than 0.5W
- Compliant with MSA SFP28
- Electrical Interface: 20 pins edge connector
- Management Interface: Serial, I²C
- Connector is compatible with SFF-8432 specification
- Compatible with CISCO, D-LINK, ENTERASYS, FINISAR, FORCE 10, NETGEAR, NORTEL, RIVERSTONE, ZTE, ZYXEL etc.
- DDM Support: no

Package contents

- SFP28 25G DAC cable

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm ³
Packaging Unit Carton	80	1,200.00	48.00	48.00	38.00	87,552.00
Packaging Unit Inside	1	15.00	0.00	0.00	0.00	0.00
Packaging Unit Single	1	15.00	32.00	32.00	4.00	4,096.00
Net single without Packaging	1	0.27	5.80	1.40	1.10	0.00

More images:

