


Intel Core i5 12600KF - 3.7 GHz - 10 Kerne - 16 Threads

20 MB Cache-Speicher - LGA1700 Socket - OEM

Gruppe	Prozessoren
Hersteller	Intel
Hersteller Art. Nr.	CM8071504555228
EAN/UPC	0675901979160



Beschreibung

Intel Core i5 12600KF - 3.7 GHz - 10 Kerne - 16 Threads - 20 MB Cache-Speicher - LGA1700 Socket - OEM

Hauptmerkmale

Produktbeschreibung	Intel Core i5 12600KF / 3.7 GHz Prozessor - OEM
Produkttyp	Prozessor
Prozessortyp	Intel Core i5 12600KF (12. Gen.)
Anz. der Kerne	10 Kerne / 16 Threads
Cache-Speicher	20 MB
Geeignete Sockel	LGA1700 Socket
Prozessoranz.	1
Taktfrequenz	3.7 GHz
Max. Turbo-Taktfrequenz	4.9 GHz
Herstellungsprozess	14 nm
Funktionen	Enhanced SpeedStep technology, Hyper-Threading-Technologie, Unterstützung für Execute Disable Bit, Intel Virtualization Technology, Intel 64 Technology, Streaming-SIMD-Erweiterungen 4.1, Streaming-SIMD-Erweiterungen 4.2, Intel Turbo Boost Technology 2.0, Intel AES New Instructions (AES-NI), Thermal Monitoring Technologies, Intel Virtualization Technology for Directed I/O (VT-d), Idle States, Intel VT-x with Extended Page Tables (EPT), Intel Secure Key, Intel Advanced Vector Extensions 2 (AVX2.0), Intel OS Guard, Intel Speed Shift Technology, Intel Optane Memory Supported, Mode-based Execute Control (MBE), Intel Volume Management Device (VMD), Intel Boot Guard, Intel Deep Learning Boost (DL Boost), Intel Control-Flow Enforcement Technology, Intel Gaussian and Neural Accelerator 3.0, Intel Thread Director, Instruction Set 64-bit

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.