Panasonic BUSINESS



iA (intelligent Auto) H.265 Compact Dome Camera

Panasonic WV-S3131L is a compact & simple design multifunction camera that achieves high visibility even under extreme conditions and can be placed in a small space without damaging the landscape. Intelligent Auto (iA) allows the camera to automatically adjust the key settings in real-time depending on the scenery and movement, reducing distortion such as motion blur and moving objects. New industry-leading 144dB dynamic range delivers balanced scene exposure in dynamic and extreme-backlit lighting environments. In addition, color night vision provides outstanding low-light performance with accurate color rendition and saturation from i-Pro's 1/3" sensor, rivaling the performance of costlier 1/2" sensor cameras in the market. The adopted H.265 Smart Coding technology, intelligently reduces bandwidth efficiency of up to 95%* more than conventional H.264 for longer recording and less storage. Cameras out-of-the-box, support full data encryption streaming and is compliant to FIPS 140-2 Level 1 standards to keep your video secured.

*Value in Advanced mode with Smart Facial Coding depends on scene.

Extreme image quality allows evidence to be captured even under challenging conditions

- Auto Shutter speed control for fast moving objects with Intelligent Auto
- Sharp and clear images of a walking person day & night
- Outstanding low light performance in true color with low noise for night time applications
- Super Dynamic 144dB for backlit situations on entrance.
- Built-in IR LED to produce a clear monochrome image in 0 lux conditions with 15 m (49 feet) irradiation distance
- Wide area surveillance even in compact design. moreover, corridor mode to survey vertically long area.

Extreme H.265 compression with new Smart Coding

- Longer recording and less storage compared to any H.264 based compression techniques
- New self-learning ROI* encoding (Auto VIQS) detects movement within the image and compresses the areas with little motion in order to reduce transmitted data while maintaining the quality of the image.
- New "Smart Facial Coding" adds more bandwidth reduction for ID camera applications mainly capturing faces
 *Region of Interest

Extreme Data Security

- Full encryption microSDXC/microSDHC/microSD card edge recording to keep your data safe
- FIPS 140-2 Level 1 compliant
- Full end-to-end system encryption with supported VMS and devices to protect from IP snooping/spoofing and detect data alteration

Key Features

- Full HD 1080p 60fps
- iA (intelligent Auto)
- Extreme Super Dynamic 144dB
- Color night vision (0.0019 to 0.03 lx)
- H.265 Smart Coding
- Built-in IR LED
- Corridor mode

(90 degrees or 270 degrees in image rotation)

Industry examples

- Education
- Retail
- Bank (ATM)
- Building






Coocifications

Camera	Image S	ensor	Approx. 1/3 type CMOS image sensor
J ao.a	Minimum Illumination		Color : 0.03 lx, BW : 0.015 lx
	IVIII III III III III III III III III I		(F2.3, Maximum shutter : Off (1/30s), AGC : 11)
			BW : 0 lx
			(F2.3, Maximum shutter: Off (1/30 s), AGC: 11, when the IR LED is li
			Color: 0.0019 lx, BW: 0.0009 lx
			(F2.3, Maximum shutter : max. 16/30s, AGC : 11) *1
	White Balance		AWC (2,000 - 10,000 K), ATW1 (2,700 - 6,000 K), ATW2 (2,000 - 6,000 K)
	Maximum shutter		Max. 1/10000 s to Max. 16/30 s
	Intelligent Auto		On / Off
	Super Dynamic*2		On / Off, the level can be set in the range of 0 to 31.
	Dynamic Range		144 dB typ. (Super Dynamic : On)
	Adaptive Black Stretch		The level can be set in the range of 0 to 255.
	Back light compensation /		BLC (Back light compensation) / HLC (High light compensation) / Off
	High light compensation		(only when Super dynamic / Intelligent Auto : Off)
	Fog compensation		On / Off (only when Intelligent auto / auto contrast adjust : Off)
	Maximum gain		The level can be set in the range of 0 to 11.
	Color/BW (ICR)		Off / On (IR Light Off) / On (IR Light On) / Auto1 (IR Light Off) / Auto2 (IR Light On) / Auto3 (SCC
	IR LED Light		High / Middle / Low / Off, Maximum irradiation distance : 15 m (Approx. 49 ft)
	Digital Noise Reduction		The level can be set in the range of 0 to 255.
	Video Motion Detection (VMD)		On / Off, 4 areas available
	Intelligent VMD (i-VMD)*3		Type 4 *optional plug-in software WV-SAE200
	Privacy Zone		On / Off (up to 8 zones available)
	Image rotation*4		0 ° / 90 ° / 180 °(Upside-down) / 270 °
	Mirror		On / Off
	Camera Title (OSD)		On / Off Up to 20 characters (alphanumeric characters, marks)
1	Zoom Ratio		1 x Optical
Lens			Choose from 3 levels of x1, x2, x4
	Digital (electronic) zoom Focal length		2.8 mm {1/8 inches}
			[16 : 9 mode] Horizontal : 108°
	Angular Field of View		
			[4 : 3 mode] Horizontal : 89°
			Vertical : 66°
	Maximum Aperture Ratio		1:2.3
	Focus range		0.5 m {19-11/16 inches} – ∞
Adjusting Angle			Horizontal (PAN) angle: ±45°, Vertical (TILT) angle: 0 to +90°,
			Azimuth (YAW) angle: ±90°
Browser			Brightness
GUI Network	GUI /		English, Italian, French, German, Spanish, Portuguese, Russian,
	Setup Menu Language		Chinese, Japanese
			10Base-T / 100Base-TX, RJ45 connector
	Resolution		•2 mega pixel [16 : 9] (30/60 fps)
	H.265/ H.264		1,920 x 1,080 / 1,280 x 720 / 640 x 360 / 320 x 180
	JPEG (MJPEG)		•3 mega pixel [4 : 3] (30 fps)
			2,048 x 1,536°5 / 1,280 x 960 / 800 x 600 / 640 x 480 / 400 x 300 / 320 x 240
	H.265/	Transmission Mode	Constant bit rate / VBR / Frame rate / Best effort
	H.264*6	Transmission Type	Unicast / Multicast
		Image Quality	10 steps
	Smart Coding		GOP(Group of pictures) control
			[When H.264 is selected] Off / On(Low) / On(Mid)
			[When H.265 is selected] Off / On(Low) / On(Mid) /
			On(Advanced) / On(Frame rate control)
			Smart Facial Coding*
			_
			Off / On(AUTO VIQS) / On(Smart Facial Coding)
			*Smart Facial Coding is only available with Stream(1).

Network	Audio Compression	G.726 (ADPCM) : 16 kbps / 32 kbps
	·	G.711 : 64 kbps
		AAC-LC*7 : 64 kbps / 96 kbps / 128 kbps
	Supported Protocol	IPv6: TCP/IP, UDP/IP, HTTP, HTTPS, RTP, FTP, SMTP, DNS, NTP, SNMP, DHCPv6, MLD, ICMP, ARP, IEEE 802.1X, DiffServ
		IPv4: TCP/IP, UDP/IP, HTTP, HTTPS, RTSP, RTP, RTP/RTCP, FTP, SMTP, DHCP, DNS, DDNS, NTP, SNMP, UPnP, IGMP, ICMP, ARP, IEEE 802.1X, DiffServ
	No. of Simultaneous Users	Up to 14 users (Depends on network conditions)
	microSDXC/microSDHC/	H.265 / H.264 recording :
	microSD	Manual REC / Alarm REC (Pre/Post) / Schedule REC /
	Memory Card*8*9	Backup upon network failure
		JPEG recording :
		Manual REC / Alarm REC (Pre/Post) / Backup upon network failure
		Compatible microSDXC/microSDHC/microSD Memory Card :
		Panasonic 2 GB, 4 GB*, 8 GB*, 32 GB*, 64 GB**model
		*microSDHC card, **microSDXC card
	Mobile Terminal Compatibility	iPad, iPhone, Android™ mobile terminals
Alarm	Alarm Source	VMD alarm*10, Command alarm, Audio detection alarm
	Alarm Actions	microSDXC/microSDHC/microSD memory recording, E-mail notification
		HTTP alarm notification Indication on browser, FTP image transfer,
		Panasonic alarm protocol output
Input/ Output	Built-in microphone	Nondirectional electret condenser microphone
General	Safety	UL (UL60950-1 2Ed), c-UL (CAN/CSA C22. NO.60950-1-07), CE, IEC60950-
	EMC	FCC (Part15 Subpart B, ClassA, SDoC), ICES-003 ClassA,
		EN55032 ClassB, EN55024
	Power Source and	PoE (IEEE802.3af compliant) Device :
	Power Consumption	DC48 V 80 mA, Approx. 3.8 W (Class 2 device)
	Ambient Operating	0 °C to +40 °C (32 °F to 104 °F)
	Temperature	
	Ambient Operating Humidity	10 to 90 % (no condensation)
	Dimensions	ø104 mm x 51 mm (H) {ø4-3/32 inches x 2 inches (H)}
		Dome radius 27 mm {1-1/16 inches}
	Mass (approx.)	Approx. 255 g {0.56 lbs}
	Finish	Main body : ABS resin, Sail white
		Dome section : Polycarbonate resin, Clear

- *1 Converted value
- *2 Super Dynamic function is automatically set off on 60 fps mode.
- *3 Smart Facial Coding, i-VMD can not be used at the same time.
- *4 Settings of [90 °] and [270 °] are only available for the [16 : 9 mode].
- *5 Used by super resolution techniques
- *6 Transmission for 4 streams can be individually set.
- *7 When recording audio on an microSDXC/microSDHC/microSD memory card, only use AAC-LC (Advanced Audio Coding - Low Complexity).
- *8 The replacement cycle (target) of a microSD memory card differs from that of a standard size SD memory card. For details, check the content of the Panasonic Support website
- (https://security.panasonic.com/support/info/(Control No.: C0117>).
- *9 For details, check the content of the Panasonic Support Web Site $(\ https://security.panasonic.com/support/info/ < Control No.: C0107 > < Control No.: C0306 > < Control No.: C0307 >)$
- *10 Including alarms from Plug-in Software

Appearance



Optional Accessory

Plug-in Software for i-VMD

WV-SAE200

i-VMD is possible to detect objects in the specified area by advanced video analysis technology.

i-VMD: Intruder Detection, Loitering Detection, Direction Detection, Scene Change Detection, Object Detection, Cross Line Detection



Trademarks and registered trademarks

- iPad and iPhone are trademarks of Apple Inc., registered in the U.S. and other countries.
 Android is a trademark of Google LLC.
- ONVIF and the ONVIF logo are trademarks or registered trademarks of Onvif Inc.
 All other trademarks identified herein are the property of their respective owners.

- Safety Precaution: Carefully read the Important Information, Installation Guide and operating instructions before using this product.
- Panasonic cannot be responsible for the performance of the network and/or other manufacturers' products used on the network.
- Masses and dimensions are approximate. Specifications are subject to change without notice.

DISTRIBUTED BY:

Panasonic

