

### Einsatzempfehlung

Material	Stahl N/mm <sup>2</sup>				Rostfreie Stähle		Guss		NE-Metalle			Superleg.		Stahl gehärtet	
Zugfestigkeit	<500	<800	<1200 (<HRC38)	<1600 (<HRC48)	<800	<1200	GG	GGG	Al Knetleg.	Al Si<10%	Cu, Ms	Ti/Ni/Co <900	900-1500	HRC 48-57	HRC 58-63
40 00 601 339 - Vc (m/min)	30	28							35		35				
40 00 601 389 - Vc (m/min)	32	30			9				35		70				
40 00 601 418 - Vc (m/min)	30	28	8	4	7	7	15	18	35		60	7	6		
Kühlung	Emulsion	Emulsion	Emulsion	Schneidöl	Schneidöl	Schneidöl	Emulsion	Emulsion	Emulsion		Emulsion	Schneidöl	Schneidöl		